

Heavy-Duty Power Extension Cord for PDU and UPS, 20A, 12AWG (IEC-320-C19 to NEMA L6-20P), 10-ft.

MODEL NUMBER: **P040-010**



Highlights

- C19 to L6-20P power cord, 10 ft.
- 12AWG, SJT, 20A, 250V
- RoHS compliant

Package Includes

- 10 ft. C19 to L6-20P Power Cord

Description

Tripp Lite's Heavy Duty C19 to L6-20P 10 ft. power cord is constructed with 3 x 12AWG copper conductors, fully molded ends, and 250V/20A rating.

Features

- Molded, Heavy-Duty Power Cord, 10 ft.
- IEC-320-C19 to NEMA L6-20P
- 12AWG, SJT, 20A, 250V
- RoHS compliant

Specifications

INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.1
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	NEMA L6-20P



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Side B - Connector 1	IEC-320-C19
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>