EAO – Your Expert Partner for Human Machine Interfaces

44-800.2 - Lever switch complete

Ø 22.5 mm

raised

round

Ø 22 mm

0.080 kg

IP 65

Solder 2.8 x 0.5 mm

Momentary

44-800.2 - Lever switch complete



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting cut-out Design

Front Front shape Front dimension

Other Attributes Weight

Operating-/Indication part Lever colour black Lever material Plastic

IP-Rating Front protection

Connection Method Terminal

Actuator Switching action

Switching element

Switching voltage Switching current Contacts Switching system Contact material 250 V AC 5 A 2 NC + 2 NO Snap-action switching element Gold


Function Lever switch




EAO – Your Expert Partner for Human Machine Interfaces

44-800.2 - Lever switch complete


Dimensions




Mounting cut-outs



Wiring diagram



Component layout



Additional information

2 positions without latch position With flat receptacle, VDE 0630 (SEV) specify use of insulating sleeve Part No. 280-0010-00

Legend

Contacts: NC = Normally closed, NO = Normally open Switching action: B = Momentary

