

**Item # 240211AAAB, 2 1/2" New Big Look Time Meter Hours Non-Reset**



[larger image](#)

Specifications	<a href="#">Product Overview</a>
<b>Model</b>	240 Series Time Meters
<b>Case Style</b>	New Big Look
<b>Size</b>	2-1/2 in
<b>Period Measured and Type</b>	Hours Non-Reset
<b>Rating</b>	120 V 60 Hz
<b>Mounting Style</b>	4 Mounting Studs

<a href="#">Specifications</a>	Product Overview
<b>Accuracy</b>	Matches frequency control of power system.
<b>Vibration Shock</b>	Meets ANSI Specification C39.1
<b>Material</b>	Brass terminal studs Case of clear Polycarbonate Frame of black Polycarbonate Polycarbonate front covers.
<b>Safety</b>	Type 240 elapsed-time meters are recognized under the Component Program of Underwriters' Laboratories. (UL File #E91703) & CSA
<b>Input Range</b>	All Type 240 models available to operate on 120 or 208/240 or 480 volts AC, 50 or 60 Hertz.
<b>Sealing</b>	All non-reset Type 240 models are weather resistant. Sealed window and no-through screw holes for flange or back-of panel mounting protect motor, counter, and gearing from rain or panel wash-down.
<b>Presentation</b>	6-digit counter in 5/32" high hours and tenths of hours or minutes and tenths of minutes.
<b>Insulation Level</b>	Operating at 120, 208, 240 or 480 volts AC, will pass Hi-pot of 2000 V <sub>RMS</sub> for one minute.
<b>Burden Data</b>	3 VA typical
<b>Features</b>	<ul style="list-style-type: none"> <li>• Back-of-panel model</li> <li>• 2 1/2" and 3 1/2" New Big Look models</li> <li>• 2 1/2" and 3 1/2" Round and Square models</li> <li>• Conduit-case models</li> <li>• Complete interchangeability physically and electrically with most GE Types 235 and 236 models</li> <li>• Optional 3 stud mounting is available on 3 1/2" New Big Look style 240 meters only.</li> </ul>