



Representative

Catalog Number: 370
Product ID: 7TAD013090R0000
UPC Number: 78621000370
EAN Number: 05414363141556
Status: Active

1/2 Inch Hub Connector, Steel Electro Zinc Plated, Nylon Insulated for Use with Rigid/IMC Conduit

- Rugged steel/malleable iron construction
- Tapered internal threads for water-tight/dust-tight union
- Threads relieved to prevent bottoming of conduit, ensuring sound assembly
- Recessed sealing ring at box end; sealing ring captivated
- Hardened steel/malleable iron/copper-free aluminum locknuts designed to provide high quality ground continuity; extended reach of locknut permits clamping on thin boxes and enclosures
- Insulated throat, insulates conductors, prevents abrasion and thinning of conductor insulation, reduces wire pull effort
- To positively bond conduit to box or enclosure.
- Suitable for hazardous locations use in Class I, Division 2; Class II, Division 1 & 2; Class III, Division 1 & 2 per NEC 501-4(b); 502-4 (a) and 503-3 (a).
- Suitable for hazardous locations use in Class II, Groups E, F, G & Class III locations per CEC 18-202; 18-252; 18-302; 18-352.
- When used with neoprene O-ring, provides watertight threaded hub on enclosures
- UL Listed 105 degree C

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	T&B
Type	Hub Connector
Special Features	Rain Tight and CSA Certified Watertight and Dust Tight
Application	To Connect Threaded Metal Conduit to a Threadless Opening in a Box or Enclosure
Standard	UL E23018, CSA
Size	1/2 Inch
Material	Steel
Finish	Zinc Plated
Temperature Rating	UL Listed 105 Degrees C

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	Internal thread
Connection type screw connection to housing	Thread
Thread type	NPT

One-piece	N
Material housing	Steel
Surface protection	Other
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y
Operating temperature	0-+105°C

Packaging

Inner Quantity	25
Inner Dimensions (inches)	4x4.5x6
Outer Quantity	100
Outer Dimensions (inches)	9.75x9.25x7.25
Weight Uom	25 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com