89898-312LF - DUBOX™ : 24 Position Vertical Card Connector, Surface Mount, Double row, Dual entry





Mating Half

▶77313-101-24LF
▶95278-101-24LF

Specifications

G	er	ıe	er	al	

General	
Hold Down Style	No Locating Pegs
Number of contacts (per row)	12
Number of contacts (Total)	24
Number of rows	2
Orientation	Vertical
Packaging	Tube
Mating half	Mates with 0.64 mm (0.025 in.) Square pins.
Series Number	89898
Dimensional	
Thickness (Board)	1.6 mm (0.062 in.) or 2.36 mm (0.093 in.)
Footprint (Board)	2.54 mm x 7.2 mm (0.1 in. x 0.283 in.)
Electrical	
Current rating	3A max. per Contact/2A max. per Contact for Full Load
Resistance (Contact)	15 milli ohms Initial, 20 milli ohms After test
Resistance (Insulation)	100000 M-ohms
Voltage rating	1000V rms
Mechanical	
Insertion force	1.50N (150 gf) per Contact
Withdrawal Force	0.3N (30 gf) min. per Contact
Mounting	
Solder process	Compatible with Wave, Vapor - Phase
Physical	Conv
Color (Housing)	Grey
Material (Contact)	Phosphor Bronze
Material (Housing)	High Temperature Thermoplastic
Plating (Contact area)	0.76 μm (30 μin.) Gold
Plating (Tail)	2.54 μm (100 μin.) Tin
Underplating (Contact)	1.27 μm (50 μin.) Nickel
Flammability rating	UL 94 V-0

Temperature (Range)	-65 °C to +125 °C			
Approvals / Certifications				
UL File Number	E66906			
Approvals / Certifications	UL and CSA Approved			



