



Family

Catalog Number: MSC500
Product ID: 7TAA017430R0003
UPC Number: 78621081774
EAN Number: 05415022255447
Status: Active

Motor Stub Splice Insulator 350 AWG - 500 kcmil, Bolt Max Length 1-3/4 inch

- Re-enterable motor stub insulator.
- Easy installation. No special tools required.
- Insulate motor stub splices quickly and dependably.

North American Specifications (UNSPSC)

UNSPSC	39121721 Electrical insulators
IGCC	5069 Electrical insulators
Brand Name	Shrink-Kon
Type	Splice Insulators and Insulating Covers
Special Features	Re-enterable motor stub insulator.
Application	Insulate motor stub splices quickly and dependably.
Voltage Rating	600V
Material	Body - Modified Neoprene Elastomer, Straps - Nylon

European Specifications (ETIM)

ETIM	EC002254 Cable insulation hose
Inner diameter	65.0748mm
Colour	Black
Heat-resistant	N
Stretch sleeve	N

Packaging

Outer Quantity	5
Outer Dimensions (inches)	11.4x8.3x6.4
Weight Uom	51 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000523

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com