



Representative

**Catalog Number:** 256-30695-1095  
**Product ID:** 7TAH007970R0021  
**UPC Number:** 78621006230  
**EAN Number:** 05414363139607  
**Status:** Active

Copper Two-Hole Lug, Standard Barrel, Peep Hole, Tongue Length 1.31 Inches, Max 35kV, Wire Size #6 AWG, 1/4 Inch Bolt Size, 3/4 Inch Hole Spacing, Tin Plated, Die Color Code Blue, Die Code 24

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Standard Barrel Copper Lug
Standard	UL E9809, CSA 4503
Cable Size	#6 AWG
Stud Size	1/4
Number Of Holes	2
Material	Copper
Color	Blue

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	2

### Packaging

Outer Quantity	100
Outer Dimensions (inches)	4.2x3.5x2.6
Weight Uom	1.81 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com