




85853-1136LF : 85853-1136LF  
METRAL HDR 5RX2M SIG PF

Product Image  
Unavailable



[www.fci.com](http://www.fci.com)

PRODUCT NUMBER
85853-XYX OR 85853-XYXX
85853-XYXLF OR 85853-XYXXLF



mat'l code				tolerances unless otherwise specified				CUSTOMER			FCJ www.fciconnect.com							
ltr	ecn no.	dr	date	linear	0.X ±0.3			COPY			title							
CW	V06-0569	DCH	2006-06-13		0.XX ±0.13			projection			METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT							
CX	DG09-0256	TER	2009-08-19		.XXX ±.051						product family							
-	-	-	-	angles	0° ±2°						METRAL							
CS	V04-0408	TAB	04/27/04	dr	T.BRUNGARD	11/19/99	MM			code								
CT	V04-0353	DAI	05/02/04	enrg	M.STRAWSER	11/19/99	2:1			size								
CU	V04-0559	HTB	06/01/04	chr	M.STRAWSER	11/19/99	A			dwg no								
CV	V04-1100	DAI	01/25/05	appd	M.STRAWSER	02/29/00	2:1			85853								
sheet index	revision	CX	CX	CX	CX	CX	CX	CX	CX	CX	CX	CX	CX	CX	CX	CX	CX	213
	sheet	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15		1 of 15




This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCJ. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCJ. Copyright FCJ.

1 | 2

3 |

4



REQUIRED PC BOARD LAYOUT  
COMPONENT SIDE  
SEE PRINT 58351 FOR  
ADDITIONAL PCB INFORMATION

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
5	5.00	13.60
6	5.75	13.60
7	6.50	13.60
8	7.25	13.60
9	5.00	17.00
10	5.75	17.00
19	8.00	4.30
20	8.00	13.60
21	8.00	17.00
25	5.75	15.60
33	7.25	12.90
36	5.75	14.40
49	5.75	15.10
64	5.75	14.90
67	7.25	16.30



This document is the property of and embodies  
 CONFIDENTIAL and PROPRIETARY information of FCJ.  
 No part of the information shown on this  
 document may be used in any way or disclosed  
 to others without the written consent of FCJ.  
 Copyright FCJ.

mat'l code				tolerances unless otherwise specified		CUSTOMER		www.fcjconnect.com	
ltr	ecr no.	dr	date	linear	0.X ±0.3		COPY		title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT
CX					0.XX ±0.13		projection		
					.XXX ±.051				
				angles	0° ±2°				product family METRAL code size 213 dwg no 85853 sheet 2
		dr	T.BRUNGARD	11/19/99	MM		scale 1:1		
		enr	M.STRAWSER	11/19/99	A				
		chr	M.STRAWSER	11/19/99					
		appd	M.STRAWSER	02/29/00					
sheet index	revision sheet								

cage code 22526

Pro/E

3 |

4

PDM: Rev: CX

STATUS: Released

Printed: Jan 17, 2011



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCJ. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCJ. Copyright FCJ.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X01 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X02 SEE NOTE 10 LEAD FREE OPTION	E	3	3	19	3	3	19	3	3	19	3	3	19
	D	3	19	3	3	19	3	3	19	3	3	19	3
	C	19	3	3	19	3	3	19	3	3	19	3	19
	B	3	3	19	3	3	19	3	3	19	3	3	19
	A	3	19	3	3	19	3	3	19	3	3	19	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X03 SEE NOTE 10 LEAD FREE OPTION	E	19	3	19	3	19	3	19	3	19	3	19	3
	D	3	19	3	19	3	19	3	19	3	19	3	19
	C	19	3	19	3	19	3	19	3	19	3	19	3
	B	3	19	3	19	3	19	3	19	3	19	3	19
	A	19	3	19	3	19	3	19	3	19	3	19	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X04 SEE NOTE 10 LEAD FREE OPTION	E	10	10	10	10	10	10	10	10	10	10	10	10
	D	10	10	10	10	10	10	10	10	10	10	10	10
	C	10	10	10	10	10	10	10	10	10	10	10	10
	B	10	10	10	10	10	10	10	10	10	10	10	10
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X05 SEE NOTE 10 LEAD FREE OPTION	E	7	6	5	5	5	5	5	5	5	5	5	5
	D	7	6	5	5	5	5	5	5	5	5	5	5
	C	7	6	5	5	5	5	5	5	5	5	5	5
	B	7	6	5	5	5	5	5	5	5	5	5	5
	A	7	6	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X06 SEE NOTE 10 LEAD FREE OPTION	E	25	25	25	25	25	25	25	25	25	25	25	25
	D	25	25	25	25	25	25	25	25	25	25	25	25
	C	25	25	25	25	25	25	25	25	25	25	25	25
	B	25	25	25	25	25	25	25	25	25	25	25	25
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X07 SEE NOTE 10 LEAD FREE OPTION	E	33	7	7	7	7	7	7	7	7	7	7	7
	D	36	7	7	7	7	7	7	7	7	7	7	7
	C	33	7	7	7	7	7	7	7	7	7	7	7
	B	36	7	7	7	7	7	7	7	7	7	7	7
	A	33	7	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X08 SEE NOTE 10 LEAD FREE OPTION	E	4	1	1	1	19	1	1	1	1	19	1	1
	D	3	1	1	1	19	1	1	1	1	1	1	1
	C	3	1	1	1	19	1	1	1	1	19	1	1
	B	3	1	1	1	19	1	1	1	1	19	1	1
	A	3	1	1	1	19	1	1	1	1	19	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X09 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	4	4	4	4	4	4	4	4	4	4	4	4
	B	1	2	2	2	2	2	2	1	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X10 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	20	6
	D	6	6	6	6	6	6	6	6	6	6	20	6
	C	6	6	6	6	6	6	6	6	6	6	20	6
	B	6	6	6	6	6	6	6	6	6	6	20	6
	A	6	6	6	6	6	6	6	6	6	6	20	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X11 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	4	2	4	2	2	19	2
	D	2	2	2	2	2	4	2	4	2	2	19	2
	C	2	2	2	2	2	4	2	4	2	2	19	2
	B	2	2	2	2	2	4	2	4	2	2	19	2
	A	2	2	2	2	2	4	2	4	2	2	19	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X12 SEE NOTE 10 LEAD FREE OPTION	E	8	8	8	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	20	20	20	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	8	8	8	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X13 SEE NOTE 10 LEAD FREE OPTION	E	4	4	4	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	19	19	19	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	4	4	4	2	2	2	2	2	2	2	2	2

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		 www.fcjconnect.com	
ltr	ecr no.	dr	date	linear	0.X ±0.3	COPY		title	
CX					0.XX ±0.13	projection		METRAL SIGNAL HEADER	
				angles	.XXX ±.051			2 MOD, 5 ROW PRESS-FIT	
				dr	0° ±2°			product family	
				engr	T.BRUNGARD 11/19/99	MM		METRAL	
				chr	M.STRAWSER 11/19/99			code	
				appd	M.STRAWSER 02/29/00	scale		213	
sheet	revision					1:1		size	
index	sheet					A		85853	
								sheet	
								3	



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCJ. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCJ. Copyright FCJ.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X14 SEE NOTE 10 LEAD FREE OPTION	E	1	4	1	1	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	4	1	4	3	1	1	1
	C	1	1	1	4	1	1	1	4	3	3	1	1
	B	1	4	1	1	1	1	1	4	3	3	1	1
	A	1	1	1	1	1	4	1	4	1	4	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X15 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	4	1	1	1	4	1	1	1	1
	D	1	4	1	1	1	1	4	1	1	1	1	4
	C	1	1	1	1	4	1	1	1	1	4	1	1
	B	1	1	4	1	1	1	1	4	1	1	1	1
	A	1	1	1	1	1	4	1	1	1	1	1	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X16 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	3	3	1	3	1	1	1
	D	1	1	1	1	1	3	3	1	3	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1
	A	4	4	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X17 SEE NOTE 10 LEAD FREE OPTION	E	1	4	1	1	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	4	1	4	3	4	1	1
	C	1	1	1	4	1	1	1	4	3	3	1	1
	B	1	4	1	1	1	1	1	4	3	3	1	1
	A	1	1	1	1	1	4	1	4	3	4	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X18 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	4	1	1	1	4	1	1	1	1
	D	1	4	1	1	1	1	4	1	1	1	1	1
	C	1	1	1	1	4	1	1	1	1	4	1	1
	B	1	1	4	1	1	1	1	4	1	1	1	1
	A	4	4	1	1	1	4	1	1	1	1	1	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X19 SEE NOTE 10 LEAD FREE OPTION	E	25	25	25	25	25	25	25	25	25	25	25	25
	D	25	25	25	25	25	25	25	25	25	25	25	25
	C	25	25	25	25	25	25	25	25	25	25	25	25
	B	25	25	25	25	25	25	25	25	25	25	25	25
	A	25	25	25	25	25	25	25	25	25	25	25	25

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X20 SEE NOTE 10 LEAD FREE OPTION	E	3	2	2	2	2	2	3	2	2	2	2	2
	D	3	2	2	2	2	2	2	2	2	2	2	3
	C	3	2	2	2	4	4	4	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X21 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	19	2	2
	D	2	2	2	2	2	2	2	2	2	19	2	2
	C	2	2	2	2	2	2	2	2	2	19	2	2
	B	2	2	2	2	2	2	2	2	2	19	2	2
	A	2	2	2	2	2	4	2	4	2	19	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X22 SEE NOTE 10 LEAD FREE OPTION	E	4	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	19	19	19	2	2	19	2	2	2	2	2	2
	B	2	2	2	2	2	4	2	2	2	2	2	2
	A	4	2	2	2	2	4	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X23 SEE NOTE 10 LEAD FREE OPTION	E	49	49	49	49	49	49	49	49	49	49	49	49
	D	49	49	49	49	49	49	49	49	49	49	49	49
	C	49	49	49	49	49	49	49	49	49	49	49	49
	B	49	49	49	49	49	49	49	49	49	49	49	49
	A	49	49	49	49	49	49	49	49	49	49	49	49

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X24 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	20	6	6
	D	6	6	6	6	6	6	6	6	6	20	6	6
	C	6	6	6	6	6	6	6	6	6	20	6	6
	B	6	6	6	6	6	6	6	6	6	20	6	6
	A	6	6	6	6	6	8	6	8	6	20	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X25 SEE NOTE 10 LEAD FREE OPTION	E	8	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	20	20	20	6	6	20	6	6	6	6	6	6
	B	6	6	6	6	6	8	6	6	6	6	6	6
	A	8	6	6	6	6	8	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X26 SEE NOTE 10 LEAD FREE OPTION	E	1	3	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	3	3

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCJ		www.fcjconnect.com	
ltr	ecr no.	dr	date	linear	0.X ±0.3	COPY		projection		title	
CX					0.XX ±0.13					METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT	
				angles	.XXX ±.051					product family	
				dr	0° ±2°			MM		METRAL	
				engr	T.BRUNGARD 11/19/99					code	
				chr	M.STRAWSER 11/19/99			size		213	
				appd	M.STRAWSER 02/29/00			dwg no		4	
sheet	revision							A		sheet	
index	sheet							85853		4	



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X27 SEE NOTE 10 LEAD FREE OPTION	E	5	7	7	7	7	7	7	7	7	7	7	7
	D	7	7	7	7	7	7	7	7	7	7	7	7
	C	7	7	7	7	7	7	7	7	7	7	7	7
	B	7	7	7	7	7	7	7	7	7	7	7	7
	A	7	7	7	7	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X28 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	-	2	-	2	-	-
	D	2	2	2	2	2	2	-	-	-	-	-	-
	C	2	2	2	2	2	2	2	2	-	2	-	-
	B	2	2	2	2	2	2	-	-	-	-	-	-
	A	2	2	2	2	2	2	2	-	2	-	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X29 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-	2	-
	D	-	-	-	-	-	-	-	-	-	-	-	-
	C	2	-	2	-	2	-	2	-	2	-	2	-
	B	-	-	-	-	-	-	-	-	-	-	-	-
	A	2	-	2	-	2	-	2	-	2	-	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2							
		1	2	3	4	5	6	7	8	9	10	11	12	
85853-X30 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	3	3	19	19	3	4	
	D	-	-	-	-	-	-	3	3	19	19	3	4	
	C	2	-	2	-	2	-	3	3	19	19	3	4	
	B	-	-	-	-	-	-	-	3	3	19	19	3	4
	A	2	-	2	-	2	-	3	3	19	19	3	4	

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X31 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	4	2	2	2	2	2
	D	-	-	-	-	-	-	4	2	2	2	2	2
	C	2	-	2	-	2	-	4	2	2	2	2	2
	B	-	-	-	-	-	-	-	4	2	2	2	2
	A	2	-	2	-	2	-	4	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X32 SEE NOTE 10 LEAD FREE OPTION	E	20	7	7	7	7	7	20	7	7	7	6	5
	D	20	7	7	7	7	7	20	7	7	7	6	5
	C	20	7	7	7	7	7	20	7	7	7	6	5
	B	20	7	7	7	7	7	20	7	7	7	6	5
	A	20	7	7	7	7	7	20	7	7	7	6	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X33 SEE NOTE 10 LEAD FREE OPTION	E	20	7	7	7	7	7	20	7	7	7	7	7
	D	20	7	7	7	7	7	20	7	7	7	7	7
	C	20	7	7	7	7	7	20	7	7	7	7	7
	B	20	7	7	7	7	7	20	7	7	7	7	7
	A	20	7	7	7	7	7	20	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X34 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	2	2	2	2	2
	D	-	-	-	-	-	-	2	2	2	2	2	2
	C	2	-	2	-	2	-	2	2	2	2	2	2
	B	-	-	-	-	-	-	-	2	2	2	2	2
	A	2	-	2	-	2	-	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X35 SEE NOTE 10 LEAD FREE OPTION	E	19	3	3	3	3	3	19	3	3	3	2	1
	D	19	3	3	3	3	3	19	3	3	3	2	1
	C	19	3	3	3	3	3	19	3	3	3	2	1
	B	19	3	3	3	3	3	19	3	3	3	2	1
	A	19	3	3	3	3	3	19	3	3	3	2	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X36 SEE NOTE 10 LEAD FREE OPTION	E	19	3	3	3	3	3	19	3	3	3	3	3
	D	19	3	3	3	3	3	19	3	3	3	3	3
	C	19	3	3	3	3	3	19	3	3	3	3	3
	B	19	3	3	3	3	3	19	3	3	3	3	3
	A	19	3	3	3	3	3	19	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X37 SEE NOTE 10 LEAD FREE OPTION	E	-	-	-	-	-	-	-	-	-	-	-	-
	D	-	-	-	-	-	-	-	-	-	-	-	-
	C	-	-	-	-	-	-	-	-	-	-	-	-
	B	-	-	-	-	-	-	-	-	-	-	-	-
	A	-	-	-	-	-	-	-	-	-	-	-	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X38 SEE NOTE 10 LEAD FREE OPTION	E	19	19	19	19	-	19	-	19	-	19	-	19
	D	19	19	19	19	-	19	-	19	-	19	-	19
	C	19	19	19	19	-	19	-	19	-	19	-	19
	B	19	19	19	19	-	19	-	19	-	19	-	19
	A	19	19	19	19	-	19	-	19	-	19	-	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X39 SEE NOTE 10 LEAD FREE OPTION	E	3	3	7	3	3	7	7	7	7	7	7	7
	D	3	3	7	3	3	7	7	7	7	7	7	7
	C	3	7	7	3	7	7	7	7	7	7	7	7
	B	3	3	3	3	3	7	7	7	7	7	7	7
	A	3	3	3	3	3	3	3	3	3	3	3	3

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
ltr	ecr no.	dr	date	linear	0.X ±0.3	COPY		projection		title	
CX				angles	0.XX ±0.13	MM				METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT	
				dr	.XXX ±.051	scale		product family		code	
				engr	0° ±2°	1:1		METRAL		213	
				chr				size		sheet	
				appd				dwg no		5	
sheet	revision							85853			
index	sheet							A			



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCJ. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCJ. Copyright FCJ.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X40 SEE NOTE 10 LEAD FREE OPTION	E	4	4	4	4	4	4	4	4	4	4	4	4
	D	4	4	4	4	4	4	4	4	4	4	4	4
	C	4	4	4	4	4	4	4	4	4	4	4	1
	B	4	4	4	4	4	4	4	4	4	4	4	4
	A	4	4	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X41 SEE NOTE 10 LEAD FREE OPTION	E	3	-	3	3	-	3	3	-	3	3	-	3
	D	3	3	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X42 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	1	1	1	1	1	1
	D	2	2	2	2	2	2	1	1	1	1	1	1
	C	1	1	1	1	1	1	2	2	2	2	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X43 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	5	5	5	5	5	5
	D	2	2	2	2	2	2	5	5	5	5	5	5
	C	1	1	1	1	1	1	6	6	6	6	5	5
	B	1	1	1	1	1	1	5	5	5	5	5	5
	A	1	1	1	1	1	1	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X44 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	5	5	5	5	5	5
	D	6	6	6	6	6	6	5	5	5	5	5	5
	C	5	5	5	5	5	5	6	6	6	6	5	5
	B	5	5	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X45 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	5	5	6	6	6	6	5	5
	B	5	5	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X46 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	1	2	2	2	2	2	2	2
	D	2	2	2	2	1	2	2	2	2	2	2	2
	C	3	3	3	3	3	3	3	3	3	3	3	3
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X47 SEE NOTE 10 LEAD FREE OPTION	E	-	5	5	-	5	5	-	5	5	-	5	5
	D	-	5	5	-	5	5	-	5	5	-	5	5
	C	-	5	5	-	5	5	-	5	5	-	5	5
	B	-	5	5	-	5	5	-	5	5	-	5	5
	A	5	5	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X48 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	3	2	2	2	2	2
	D	2	2	2	2	2	2	3	2	2	2	2	2
	C	2	2	2	2	2	2	3	2	2	2	2	2
	B	2	2	2	2	2	2	3	2	2	2	2	2
	A	2	2	2	2	2	2	3	2	2	2	1	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X49 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	2	2	2	2	2	2
	D	1	1	1	1	1	1	2	2	2	2	2	2
	C	1	1	2	2	2	2	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X50 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	5	2	2	2	2	2	2
	D	5	5	5	5	5	5	2	2	2	2	2	2
	C	5	5	6	6	6	6	1	1	1	1	1	1
	B	5	5	5	5	5	5	1	1	1	1	1	1
	A	5	5	5	5	5	5	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X51 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	5	6	6	6	6	6	6
	D	5	5	5	5	5	5	6	6	6	6	6	6
	C	5	5	6	6	6	6	5	5	5	5	5	5
	B	5	5	5	5	5	5	5	5	5	5	5	5
	A	5	5	5	5	5	5	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X52 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	19	19	19	19	1	1
	D	1	1	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	19	19	19	19	1
	B	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	19	19	19	19	1

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCJ		www.fcjconnect.com	
ltr	ecr no.	dr	date	linear	0.X ±0.3	COPY		projection		title	
CX				angles	0.XX ±0.13	MM				METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT	
				dr	.XXX ±0.051	MM		product family		code	
				engr	0° ±2°	MM		METRAL		213	
				chr	T.BRUNGARD 11/19/99	scale		size		sheet	
				appd	M.STRAWSER 11/19/99	1:1		dwg no		6	
					M.STRAWSER 02/29/00			A		85853	
sheet	revision										
index	sheet										



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X53 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	-	-	-	-	-	-	1	1
	D	-	1	1	-	-	-	-	-	-	-	1	1
	C	-	-	-	-	-	-	-	-	-	-	-	-
	B	-	1	1	-	-	1	-	1	1	-	1	1
	A	-	1	1	-	-	1	-	1	1	-	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X54 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	-	1	-	1	-	-	1	-
	D	1	1	1	1	-	1	-	1	-	-	1	-
	C	1	1	1	1	-	1	-	1	-	-	1	-
	B	1	1	1	1	-	1	-	1	-	-	1	-
	A	1	1	1	1	-	1	-	1	-	-	1	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X55 SEE NOTE 10 LEAD FREE OPTION	E	2	19	19	19	19	19	19	19	19	19	19	19
	D	2	19	19	19	19	19	19	19	19	19	19	19
	C	2	19	19	19	19	19	19	19	19	19	19	19
	B	2	19	19	19	19	19	19	19	19	19	19	19
	A	2	19	19	19	19	19	19	19	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X56 SEE NOTE 10 LEAD FREE OPTION	E	19	19	19	19	-	19	-	19	-	-	19	-
	D	19	19	19	19	-	19	-	19	-	-	19	-
	C	19	19	19	19	-	19	-	19	-	-	19	-
	B	19	19	19	19	-	19	-	19	-	-	19	-
	A	19	19	19	19	-	19	-	19	-	-	19	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X57 SEE NOTE 10 LEAD FREE OPTION	E	-	19	-	-	19	-	19	-	19	19	19	19
	D	-	19	-	-	19	-	19	-	19	19	19	19
	C	-	19	-	-	19	-	19	-	19	19	19	19
	B	-	19	-	-	19	-	19	-	19	19	19	19
	A	-	19	-	-	19	-	19	-	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X58 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	-	-	-	-	-	-	1	1
	D	-	1	1	-	-	-	-	-	-	-	1	1
	C	-	-	-	-	-	-	-	-	-	-	-	-
	B	-	1	1	-	1	-	1	1	-	1	1	1
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X59 SEE NOTE 10 LEAD FREE OPTION	E	3	-	3	3	3	3	3	3	3	3	3	3
	D	3	-	3	3	3	3	3	3	3	3	3	3
	C	-	-	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X60 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	19	-	19	-	2	-	2	-	19
	D	2	2	2	19	-	19	-	2	-	2	-	19
	C	2	2	2	19	-	19	-	2	-	2	-	19
	B	2	2	2	19	-	19	-	2	-	2	-	19
	A	2	2	2	19	-	19	-	2	-	2	-	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X61 SEE NOTE 10 LEAD FREE OPTION	E	19	2	2	2	2	2	2	2	2	2	2	2
	D	19	2	2	2	2	2	2	2	2	2	2	2
	C	19	2	2	2	2	2	2	2	2	2	2	2
	B	19	2	2	2	2	2	2	2	2	2	2	2
	A	19	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X62 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	20	-	20	-	6	-	6	-	20
	D	6	6	6	20	-	20	-	6	-	6	-	20
	C	6	6	6	20	-	20	-	6	-	6	-	20
	B	6	6	6	20	-	20	-	6	-	6	-	20
	A	6	6	6	20	-	20	-	6	-	6	-	20

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X63 SEE NOTE 10 LEAD FREE OPTION	E	20	6	6	6	6	6	6	6	6	6	6	6
	D	20	6	6	6	6	6	6	6	6	6	6	6
	C	20	6	6	6	6	6	6	6	6	6	6	6
	B	20	6	6	6	6	6	6	6	6	6	6	6
	A	20	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X64 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	-	-	-	2	2	-	-	-	-	2	-
	A	2	-	2	-	-	2	2	-	2	-	-	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X65 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	5	6	5	5	5
	D	5	5	6	5	5	5	5	5	6	5	5	5
	C	5	5	6	5	5	5	5	5	6	5	5	5
	B	5	5	6	5	5	5	5	5	6	5	5	5
	A	5	5	6	5	5	5	5	5	6	5	5	5

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
ltr	ecr no.	dr	date	linear	0.X ±0.3	COPY		projection		title	
CX				angles	0.XX ±0.13	MM				METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT	
				dr	.XXX ±.051	MM		product family		code	
				engr	0° ±2°	MM		METRAL		213	
				chr		MM		size		sheet	
				appd		MM		dwg no		7	
sheet	revision					scale		A		85853	
index	sheet					1:1					





This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X66 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	5	6	5	5	6
	D	5	5	6	5	5	5	5	5	6	5	5	6
	C	5	5	6	5	5	5	5	5	6	5	5	6
	B	5	5	6	5	5	5	5	5	6	5	5	6
	A	5	5	6	5	5	5	5	5	6	5	5	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X67 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	5	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	20	20	20
	B	6	6	6	6	6	6	6	6	6	20	6	6
	A	6	6	6	6	6	6	6	6	6	20	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X68 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	3	3	2
	C	2	2	2	2	2	2	2	2	3	3	2	2
	B	2	2	2	2	2	2	2	2	3	3	2	2
	A	2	2	2	2	2	2	2	2	3	3	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X69 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	4	2	2	2	2	2	2	2
	D	2	2	2	2	4	2	2	2	2	2	2	2
	C	2	2	2	2	4	4	4	4	4	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X70 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	4	2	2	2	2	2	2
	D	2	2	2	2	2	4	2	2	2	2	2	2
	C	2	2	2	2	2	4	2	2	2	2	2	2
	B	2	2	2	2	2	4	2	2	2	2	2	2
	A	2	2	2	2	2	4	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X71 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	3	2	2	2	2	2
	D	2	2	2	2	2	2	3	2	2	2	2	2
	C	2	2	2	2	2	2	3	2	2	2	2	2
	B	-	-	-	-	-	2	2	3	2	2	2	2
	A	2	2	2	2	2	2	3	2	2	2	1	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X72 SEE NOTE 10 LEAD FREE OPTION	E	1	4	4	4	4	19	4	2	19	19	19	2
	D	1	4	4	4	4	19	4	2	19	19	19	2
	C	19	4	4	4	4	19	4	2	19	19	19	2
	B	3	4	4	4	4	19	4	2	19	19	19	2
	A	3	4	4	4	4	19	4	2	19	19	19	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X73 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	6	5	5	5	5
	D	5	5	6	5	5	5	5	6	5	5	5	5
	C	1	1	6	1	5	5	5	6	5	5	5	5
	B	5	5	6	5	5	5	5	6	5	5	5	5
	A	5	5	6	5	5	5	5	6	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X74 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	3	3	2	2
	D	2	2	2	2	2	2	2	2	3	3	2	2
	C	2	2	2	2	2	2	2	2	3	3	2	2
	B	2	2	2	2	2	2	2	2	3	3	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X75 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	8	6	8	8	6	8	8	8	6	8	6
	B	6	6	6	6	8	6	6	6	6	6	6	6
	A	6	6	6	6	8	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X76 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	3	1	1	1	1	1	1
	D	1	1	1	1	1	3	1	1	1	1	1	1
	C	1	1	1	1	1	3	1	1	1	1	1	1
	B	1	1	1	1	1	3	1	1	1	1	1	1
	A	1	1	1	1	1	3	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X77 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	1	2	2	2	2	1	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X78 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	1	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ±0.3	COPY		projection		title	
CX				angles	0.XX ±0.13	MM				METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT	
				dr	.XXX ±.051	scale		product family		code	
				engr	0° ±2°	1:1		METRAL		213	
				chr	T.BRUNGARD 11/19/99	A		size		sheet	
				appd	M.STRAWSER 11/19/99			85853		8	
					M.STRAWSER 02/29/00						
sheet index	revision sheet										



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCJ. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCJ. Copyright FCJ.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X79 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	7	5	5	5	5	5	5
	D	5	5	5	5	5	7	5	5	5	5	5	5
	C	5	5	5	5	5	7	5	5	5	5	5	5
	B	5	5	5	5	5	7	5	5	5	5	5	5
	A	5	5	5	5	5	7	5	5	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X80 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	6	5	5	5	5	5	5
	D	5	5	5	5	5	6	5	5	5	5	5	5
	C	5	6	5	6	6	6	5	5	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X81 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	5	6	6	5	6	6	5	6	6	5	5
	B	5	5	5	5	5	6	5	5	5	5	5	6
	A	5	5	5	5	5	6	5	5	5	5	5	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X82 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	-
	D	1	1	1	1	1	1	1	1	1	1	1	-
	C	1	1	1	1	1	1	1	1	1	1	1	-
	B	1	1	1	1	1	1	1	1	1	1	1	-
	A	1	1	1	1	1	1	1	1	1	1	1	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X83 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-	2	-
	D	2	-	-	-	2	-	-	-	-	2	-	-
	C	2	-	2	-	2	-	2	-	2	-	2	-
	B	-	2	-	-	-	2	-	-	-	2	-	4
	A	2	-	2	-	2	-	2	-	2	-	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X84 SEE NOTE 10 LEAD FREE OPTION	E	-	-	4	4	4	4	4	4	4	4	-	-
	D	-	-	4	4	4	4	4	2	2	4	-	-
	C	-	-	4	2	2	4	4	4	4	4	-	-
	B	-	-	4	4	4	4	4	2	2	4	-	-
	A	-	-	4	4	4	4	4	4	4	4	-	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X85 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-	2	-
	D	-	-	-	-	-	-	-	2	2	2	2	-
	C	2	2	2	-	2	2	-	2	2	2	2	-
	B	2	2	2	-	2	2	-	2	2	2	2	-
	A	2	2	2	-	2	2	-	2	2	2	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X86 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X87 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	-	1	1
	D	1	1	1	1	1	1	1	1	1	-	1	1
	C	1	1	1	1	1	1	1	1	1	-	1	1
	B	1	1	1	1	1	1	1	1	1	-	-	-
	A	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X88 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1
	B	3	3	3	3	3	3	3	3	3	3	3	3
	A	19	19	19	19	19	19	19	19	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X89 SEE NOTE 10 LEAD FREE OPTION	E	19	19	19	19	19	19	3	19	19	19	19	3
	D	3	3	3	3	3	3	3	3	3	3	3	3
	C	1	1	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X90 SEE NOTE 10 LEAD FREE OPTION	E	3	-	3	3	3	3	3	3	3	3	3	3
	D	3	-	3	3	3	3	3	3	3	3	3	3
	C	-	-	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X91 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3	3	3
	C	1	3	3	3	3	3	3	3	3	3	3	1
	B	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	3	3

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCJ		www.fcjconnect.com	
ltr	ecr no.	dr	date	linear	0.X ±0.3	COPY		projection		title	
CX				angles	0.XX ±0.13	MM				METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT	
				dr	.XXX ±.051	scale		product family		code	
				engr	0° ±2°	1:1		METRAL		213	
				chr				size		sheet	
				appd				A		9	
								85853			
sheet	revision										
index	sheet										



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X92 SEE NOTE 10 LEAD FREE OPTION	E	-	5	5	-	5	5	-	5	5	-	5	5
	D	-	5	5	-	5	5	-	5	5	-	5	5
	C	-	5	5	-	5	5	-	5	5	-	5	5
	B	-	5	5	-	5	5	-	5	5	-	5	5
	A	-	5	5	-	5	5	-	5	5	-	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X93 SEE NOTE 10 LEAD FREE OPTION	E	8	6	6	6	6	6	6	6	6	6	6	6
	D	8	6	6	6	6	6	6	6	6	6	6	6
	C	8	6	6	6	6	6	6	6	6	6	6	6
	B	8	6	6	6	6	6	6	6	6	6	6	6
	A	8	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X94 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	4
	D	2	2	2	2	2	2	2	2	2	2	2	4
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X95 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	1	1	-	1	1	-	1	1
	D	-	1	1	-	1	1	-	1	1	-	1	1
	C	-	1	1	-	1	1	-	1	1	-	1	1
	B	-	1	1	-	1	1	-	1	1	-	1	1
	A	-	1	1	-	1	1	-	1	1	-	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X96 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-	2	-
	D	2	-	2	-	2	-	2	-	2	-	2	-
	C	2	-	2	-	2	-	2	-	2	-	2	-
	B	2	-	2	-	2	-	2	-	2	-	2	-
	A	2	-	2	-	2	-	2	-	2	-	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X97 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	1	2	2	2	2	2	2	2	2	2	2	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X98 SEE NOTE 10 LEAD FREE OPTION	E	19	1	2	2	1	2	2	2	2	2	2	19
	D	1	2	2	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	2	2	2	2	2	19
	B	2	2	2	2	2	2	2	2	2	2	2	19
	A	2	1	2	2	2	2	2	2	2	2	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X99 SEE NOTE 10 LEAD FREE OPTION	E	2	1	2	2	1	2	2	2	2	2	2	19
	D	2	2	2	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	2	2	2	2	2	19
	B	2	2	2	2	2	2	2	2	2	2	2	19
	A	2	1	2	2	2	2	2	2	2	2	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X100 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	1	1	1	1	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X101 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	8	20	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	20	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X102 SEE NOTE 10 LEAD FREE OPTION	E	4	4	3	4	3	4	4	4	3	4	3	4
	D	4	4	3	4	3	4	4	4	3	4	3	4
	C	4	4	4	4	4	4	4	4	4	4	4	4
	B	4	4	2	4	2	4	4	4	2	4	2	4
	A	4	4	2	4	2	4	4	4	2	4	2	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X103 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	4	3	4	3	4	3	3	3	3
	D	3	3	3	4	3	4	3	4	3	3	3	3
	C	3	3	3	4	2	4	2	4	3	3	3	3
	B	3	3	3	4	2	4	2	4	3	3	3	3
	A	3	3	3	4	2	4	2	4	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X104 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	2	3	3	3	3	3	3
	D	3	3	3	3	3	2	3	3	3	3	3	3
	C	3	3	3	3	3	2	3	3	3	3	3	3
	B	3	3	3	3	3	2	3	3	3	3	3	3
	A	3	3	3	3	3	2	3	3	3	3	3	3

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		www.fciconnect.com	
ltr	ecr no.	dr	date	linear	0.X ±0.3	COPY		title	
CX				angles	0.XX ±0.13	projection		METRAL SIGNAL HEADER	
				dr	.XXX ±.051			2 MOD, 5 ROW PRESS-FIT	
				engr	0° ±2°			product family	
				chr	T.BRUNGARD 11/19/99	MM		METRAL	
				appd	M.STRAWSER 11/19/99	scale		code	
					M.STRAWSER 02/29/00	1:1		213	
sheet	revision					size		sheet	
index	sheet					A		10	
						dwg no			
						85853			
						cage code			
						22526			



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X105 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	3	3	3	3	3	3	3	3	3
	D	2	2	2	3	3	3	3	3	3	3	3	3
	C	2	2	2	3	3	3	3	3	3	3	3	3
	B	2	2	2	3	3	3	3	3	3	3	3	3
	A	2	2	2	3	3	3	3	3	3	3	3	3
85853-X106 SEE NOTE 10 LEAD FREE OPTION	E	3	7	7	7	7	7	8	7	8	7	7	3
	D	3	7	7	7	7	7	8	7	8	7	7	3
	C	3	7	7	7	7	7	8	7	8	7	7	3
	B	3	7	7	7	7	7	8	7	8	7	7	3
	A	3	7	7	7	7	7	8	7	8	7	7	3
85853-X107 SEE NOTE 10 LEAD FREE OPTION	E	3	8	7	7	7	7	7	7	7	7	7	7
	D	3	8	7	7	7	7	7	7	7	7	7	7
	C	3	8	7	7	7	7	7	7	7	7	7	7
	B	3	8	7	7	7	7	7	7	7	7	7	7
	A	3	8	7	7	7	7	7	7	7	7	7	7
85853-X108 SEE NOTE 10 LEAD FREE OPTION	E	7	8	7	8	7	8	7	8	7	8	5	7
	D	7	8	7	8	7	8	7	8	7	8	5	7
	C	8	8	8	8	8	8	8	8	8	8	5	7
	B	6	8	6	8	6	8	6	8	6	8	5	7
	A	6	8	6	8	6	8	6	8	6	8	5	7
85853-X109 SEE NOTE 10 LEAD FREE OPTION	E	19	1	2	2	1	2	2	2	2	2	2	19
	D	1	2	2	2	2	2	2	2	2	2	2	19
	C	2	2	2	2	2	2	2	2	2	2	2	19
	B	19	2	2	2	2	2	2	2	2	2	2	19
	A	1	1	2	2	2	2	2	2	2	2	2	19

1 | 2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X110 SEE NOTE 10 LEAD FREE OPTION	E	-	2	-	2	-	2	-	2	-	2	-	2
	D	2	-	2	-	2	-	2	-	2	-	2	-
	C	-	2	-	2	-	2	-	2	-	2	-	2
	B	2	-	2	-	2	-	2	-	2	-	2	-
	A	-	2	-	2	-	2	-	2	-	2	-	2
85853-X111 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	5	5	5	5	5
	D	5	5	6	5	5	5	6	6	6	6	6	6
	C	6	6	6	5	5	5	6	6	6	6	6	6
	B	5	5	5	5	5	5	6	6	6	6	6	6
	A	6	6	6	6	6	6	5	5	5	5	5	5
85853-X112 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	2	1	1	1	1	1	1
	D	1	1	1	1	2	1	1	1	1	1	1	1
	C	1	1	2	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	2	1	1	1	1	1	1
	A	1	1	1	1	1	1	2	2	1	1	1	1
85853-X113 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	4	2	2	4	2	2	4	3	3	4	3	3
	C	2	2	4	2	2	4	3	3	4	3	3	3
	B	2	4	2	2	4	3	3	4	3	3	3	3
	A	2	2	2	2	2	2	2	2	2	2	2	2

3 |

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X114 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	4	3	3	3	3
	D	3	3	3	3	3	3	3	4	3	3	3	3
	C	3	3	3	3	3	3	3	4	3	3	3	3
	B	3	3	3	3	3	3	3	4	3	3	3	3
	A	3	3	3	3	3	3	3	4	3	3	3	3
85853-X115 SEE NOTE 10 LEAD FREE OPTION	E	2	2	1	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2
85853-X116 SEE NOTE 10 LEAD FREE OPTION	E	6	6	7	7	6	6	6	7	7	6	8	8
	D	6	6	7	7	6	6	6	7	7	6	8	8
	C	6	6	7	7	6	6	6	7	7	6	8	8
	B	6	6	7	7	6	6	6	7	7	6	8	8
	A	6	6	7	7	6	6	6	7	7	6	8	8
85853-X117 SEE NOTE 10 LEAD FREE OPTION	E	64	-	64	-	64	-	64	-	64	-	64	-
	D	-	64	-	64	-	64	-	64	-	64	-	64
	C	64	-	64	-	64	-	64	-	64	-	64	-
	B	-	64	-	64	-	64	-	64	-	64	-	64
	A	64	-	64	-	64	-	64	-	64	-	64	-

4

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
lfr	ecr no.	dr	date	linear	0.X ±0.3	COPY		projection		title	
CX				angles	0.XX ±0.13	MM				METRAL SIGNAL HEADER	
					.XXX ±.051	scale				2 MOD, 5 ROW PRESS-FIT	
				dr	0° ±2°	1:1		product family		METRAL code	
				enrg	T.BRUNGARD 11/19/99	A		size		213	
				chr	M.STRAWSER 11/19/99			dwg no		sheet	
				appd	M.STRAWSER 02/29/00			85853		11	
sheet index	revision sheet										

B

B

1 | 2

3 |

4



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCJ. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCJ. Copyright FCJ.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X118 SEE NOTE 10 LEAD FREE OPTION	E	6	-	6	-	6	-	6	-	6	-	6	-
	D	-	6	-	6	-	6	-	6	-	6	-	6
	C	6	-	6	-	6	-	6	-	6	-	6	-
	B	-	6	-	6	-	6	-	6	-	6	-	6
	A	6	-	6	-	6	-	6	-	6	-	6	-
85853-X119 SEE NOTE 10 LEAD FREE OPTION	E	4	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	4	4	2	2	2	2	2	2	2	2
	C	19	2	19	2	2	19	2	2	2	2	2	2
	B	2	2	2	4	2	4	2	2	2	2	2	2
	A	4	2	2	2	2	4	2	2	2	2	2	2
85853-X120 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	19	2	
	D	2	2	2	2	2	2	2	2	2	19	2	
	C	2	2	2	2	2	2	2	2	2	19	2	
	B	2	2	2	2	2	2	2	2	2	19	2	
	A	2	2	4	4	2	4	2	4	2	4	19	4
85853-X121 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	8	5	
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6
85853-X122 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	3	4	4
	D	2	2	2	2	2	2	2	2	2	2	4	4
	C	2	2	2	2	2	2	2	4	4	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	4
	A	2	2	2	2	2	2	2	1	2	4	4	

1 | 2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X123 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	4	1	
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2
85853-X124 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	1	3
85853-X125 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3	3	3
	C	19	19	19	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3	1	3
85853-X126 SEE NOTE 10 LEAD FREE OPTION	E	2	6	6	6	6	6	2	2	2	2	2	2
	D	2	6	6	6	6	6	2	2	2	2	2	2
	C	2	6	6	6	6	6	2	2	2	2	2	2
	B	2	6	6	6	21	6	2	2	2	2	2	2
	A	2	6	6	6	6	6	2	2	2	2	2	2

3 |

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X127 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	19	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2
85853-X128 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	3	19	19	
	D	2	2	2	2	2	2	2	2	2	19	19	
	C	2	2	2	2	2	2	19	19	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	19	19	
	A	2	2	2	2	2	2	2	2	1	2	19	19
85853-X129 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	3	1	
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2
85853-X130 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	7	5	
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6

4

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		 www.fcjconnect.com	
ltr	ecr no.	dr	date	linear	0.X ±0.3	COPY		title	
CX				angles	0.XX ±0.13	projection		METRAL SIGNAL HEADER	
					.XXX ±.051			2 MOD, 5 ROW PRESS-FIT	
				dr	0° ±2°			product family	
				engr	T.BRUNGARD 11/19/99	MM		METRAL	
				chr	M.STRAWSER 11/19/99			code	
				appd	M.STRAWSER 02/29/00			213	
sheet	revision					size		sheet	
index	sheet					A		12	
						85853			
						cage code		22526	
								4	

1 | 2

Pro/E

3 |

cage code 22526

4



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCJ. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCJ. Copyright FCJ.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X131 SEE NOTE 10 LEAD FREE OPTION	E	9	-	9	-	9	-	9	-	9	-	9	-
	D	9	-	9	-	9	-	9	-	9	-	9	-
	C	-	-	-	-	-	-	-	-	-	-	-	-
	B	9	-	9	-	9	-	9	-	9	-	9	-
	A	9	-	9	-	9	-	9	-	9	-	9	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X132 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6
	B	5	5	5	5	5	5	6	6	6	6	6	6
	A	5	5	5	5	5	5	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X133 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6
	B	7	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X134 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	1	1	2	2	3	3
	D	2	2	2	2	2	2	1	1	2	2	3	3
	C	2	2	2	2	2	2	1	1	2	2	3	3
	B	2	2	2	2	2	2	1	1	2	2	3	3
	A	2	2	2	2	2	2	1	1	2	2	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X135 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	1	1	1	1	1	1	1
	D	2	2	2	2	2	1	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	1	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X136 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	3	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X137 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	-	-	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X138 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	3	2	2	2	3	2	3	2	2
	D	2	2	2	3	2	2	2	3	2	3	2	2
	C	2	2	2	2	3	2	2	2	2	3	2	2
	B	2	2	2	2	2	3	2	2	3	2	2	2
	A	2	2	2	2	2	1	2	2	2	3	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X139 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X140 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	4	2	2	2	2	2	4	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X141 SEE NOTE 10 LEAD FREE OPTION	E	64	64	64	64	64	64	64	64	64	64	64	64
	D	64	64	64	64	64	64	64	64	64	64	64	64
	C	67	64	64	64	64	64	67	64	64	64	64	64
	B	64	64	64	64	64	64	64	64	64	64	64	64
	A	64	64	64	64	64	64	64	64	64	64	64	64

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X142 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	1	2	1
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X143 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	1	2	2
	C	2	2	2	2	2	2	2	2	2	2	1	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		FCJ		www.fcjconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3		COPY		title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT		
CX					0.XX ±0.13		projection				
					angles	.XXX ±.051					
				0° ±2°							
		dr	T.BRUNGARD	11/19/99	product family		METRAL		code		
		enrg	M.STRAWSER	11/19/99	size		dwg no		213		
		chr	M.STRAWSER	11/19/99	scale		A		sheet		
		appd	M.STRAWSER	02/29/00	1:1		85853		13		
sheet index	revision sheet										

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						
		1	2	3	4	5	6	7	8	9	10	11	12
85853-X144 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	1	2	2	2	2	2	2
	D	2	2	2	2	2	1	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	1	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2
85853-X145 SEE NOTE 10 LEAD FREE OPTION	E	7	6	6	6	6	6	6	6	6	6	6	6
	D	7	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6
	B	7	6	6	6	6	6	6	6	6	6	6	6
	A	7	6	6	6	6	6	6	6	6	6	6	6
85853-X146 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6
	C	7	6	6	6	6	5	5	5	5	5	5	5
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6
85853-X147 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	5	6	6	6
	D	6	6	6	6	6	6	6	6	5	6	5	6
	C	6	6	6	6	6	6	6	6	5	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	5

A

A



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

B

B

mat'l code		--		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
ltr	ecr no.	dr	date	linear	0.X ±0.3		COPY		title METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT 
CX					0.XX ±0.13		projection		
					.XXX ±.051				
				angles	0° ±2°				product family METRAL code size dwg no 213 sheet 14 scale 1:1 A 85853
		dr	T.BRUNGARD	11/19/99	MM		product family METRAL code		
		enr	M.STRAWSER	11/19/99			size dwg no		
		chr	M.STRAWSER	11/19/99	scale 1:1		A 85853		
		appd	M.STRAWSER	02/29/00			sheet 14		
sheet index	revision sheet								

PRODUCT NUMBER
85853-XYX OR 85853-XYXX
85853-XYXLF OR 85853-XYXXLF

NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL  
POLYMER 30 % GLASS.  
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:  
PHOSPHOR BRONZE.
- PLATING ON PRESS-FIT TAIL:  
85853-XYX IS SnPb  
85853-XYXLF IS SN (LEAD FREE)  
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE LEVEL SHOWN IN TABLE BELOW.
- PRODUCT MARKING:  
PART NUMBER DESIGNATION & BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES. IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P" WILL BE ADDED TO THE END OF THE PART NUMBER. EXAMPLE: XXXXX-XXXP
- PRODUCT SPECIFICATION GS-12-180  
APPLICATION SPECIFICATION BUS-20-073
- AFTER INSERTION INTO CIRCUIT BOARD WITH QUALIFIED TOOL.
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.  
  
ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING (DRAWING NO.)-NI--- OR (DRAWING NO.)-N5---WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-NI--- AND (DRAWINGS NO.)-N5---WILL NOT WITHSTAND REFLOW AND Au CONTACT SURFACE OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140°C FOR NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.
- FOR LEAD FREE PART NUMBERS, ADD AN "LF" SUFFIX.  
EXAMPLE: 85853-X01LF

PLATING IN CONTACT AREA		NOTES
DASH NUMBER	PERFORMANCE LEVEL	-
-PYY OR -PYXX	0.25 um GOLD MIN.	-
-NIYY OR -NIYXX	TELCORDIA CO (NXT)	-
-N5YY OR N5YXX	TELCORDIA UE (NXT)	-
-IYY OR -IYXX	TELCORDIA CO	-
-2YY OR -2YXX	TELECOM CLASS	-
-3YY OR -3YXX	IEC CLASS I	-
-5YY OR -5YXX	TELCORDIA UE	-
-NIYXLF OR -NIYXXLF	TELCORDIA CO (NXT) IEC CLASS I	SEE NOTE 9
-N5YXLF OR N5YXXLF	TELCORDIA UE (NXT)	SEE NOTE 9
-IYXLF OR -IYXXLF	TELCORDIA CO IEC CLASS I	SEE NOTE 9
-2YXLF OR -2YXXLF	TELECOM CLASS	SEE NOTE 9
-5YXLF OR -5YXXLF	TELCORDIA UE	SEE NOTE 9



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.



A

A

mat'l code		--	tolerances unless otherwise specified		CUSTOMER	FCI www.fciconnect.com	
ltr	ecn no.	dr	date	linear	COPY	title	
CX				linear	projection	METRAL SIGNAL HEADER 2 MOD, 5 ROW PRESS-FIT	
				angles		product family	
				dr	MM	METRAL	code
				enrg	T.BRUNGARD 11/19/99	size	213
				chr	M.STRAWSER 11/19/99	dwg no	sheet
				appd	M.STRAWSER 02/29/00	85853	15
sheet	revision				scale	A	
index	sheet				1:1		

B

B