

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 321, MIL-W-16878/5 TYPE EE, UL1180, NEMA HP3 Wire**MIL-W-16878/5 TYPE EE, UL1180, NEMA HP3 Wire**


Single conductor stranded silver plated Copper, PTFE extruded PTFE insulation.

Characteristics:

Temperature rating - 65°C to +200°C.

Voltage rating 1000 Volts. Resistant to acids, alkalis, oil, flame, moisture, solvents, and fungus. UL1180-300V-200°C.

SPECIFICATIONS

Conductor Size	18 AWG
Stranding	19/30 Silver Plated Copper
Insulation	PTFE
Nom. Wall Thickness	0.014 in
Nom. O.D.	0.080 in
UL Style	1180
UL Rating	300 V, 200°C
UL Flame Test	VW-1
Military Spec.	MIL-W-16878/5
Military Rating	-70°C to 200°C, 1000 V
RoHS Compliant	 RoHS Compliant
Color Code	Hook Up Wire Color Code Chart