



Actual

Catalog Number: NW10-12
Product ID: 7TAI029660R0011
UPC Number: 78621077084
EAN Number: 05414363934356
Status: Active

Non-Insulated High-Temperature Ring Terminal, Length .66 Inches, Width .31 Inches, Bolt Hole #12, Wire Range #12-#10 AWG, 1200 Degree Fahrenheit Maximum, Nickel Alloy, Plain Finish

- For easily installed, permanent terminations of solid, round, or stranded nichrome wires as used in toasters, heaters, etc.
- Application Tools: WT1377

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	For easily installed, permanent terminations of solid, round, or stranded nichrome wires as used in toasters, heaters, etc.
Wire Size	12-10
Voltage Rating	600V
Material	Nickel Alloy
Color	Metallic

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
AWG-range	12-10
Surface protection	Bare

Packaging

Inner Quantity	50
Inner Dimensions (inches)	1.6x.9x2.3
Outer Quantity	250
Outer Dimensions (inches)	10x8.2x6.5
Weight Uom	3.13 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com