

# Female Disconnects - T-Tap Nylon Insulated Self-Stripping



Product Number <sup>†</sup>	UPC (054007-)	Wire Wire Range (AWG)	Mates with <u>Male Tab</u> Width(W') x Thickness	L	H	W	Maximum Insulation Diameter	Terminals per:	
								Carton	Case
951X	12312	22-18	0.250 x 0.032	0.73	0.44	0.38	0.150	50	500
951K	12313	22-18	0.250 x 0.032	0.73	0.44	0.38	0.150	—	1000
952X	08427	16-14	0.250 x 0.032	0.73	0.44	0.38	0.150	50	500
952K	08428	16-14	0.250 x 0.032	0.73	0.44	0.38	0.150	—	1000
953X	12314	12	0.250 x 0.032	0.73	0.44	0.38	0.150	50	500
953K	12315	12	0.250 x 0.032	0.73	0.44	0.38	0.150	—	1000



**951**  
22-18

**Wire Range**  
Suggested Mate

MNG18-250DMI



**952**  
18-16-14

MNG14-250DMI



**953**  
12

MNG10-250DMI