

4, 5 and 8-Pin Field Wireable Connectors, Shielded, Screw Terminals



- Screw Terminals
- No Soldering Required
- IEC IP67 Protection



Housing Style	Female Part Number	Male Part Number	Features	Pinout
<p>CMB 81..</p>	<p>CMB 8141-0 CMB 8241-0</p>	<p>CMBS 8141-0 CMBS 8241-0</p>	<p>Nickel Plated Brass, PG9 cable gland, accepts 6-8 mm cable diameter, screw terminal accepts up to 18 AWG conductors, 85°C, 250 V, 4 A, Metal, fully shielded Mates with standard key 4-pin cordsets and receptacles</p>	<p>Female</p> <p>Male</p>
<p>CMB 82..</p>	<p>CMB 8151-0 CMB 8251-0</p>	<p>CMBS 8151-0 CMBS 8251-0</p>	<p>Nickel Plated Brass, PG9 cable gland, accepts 6-8 mm cable diameter, screw terminal, accepts up to 18 AWG conductors, 85°C, 60 V, 4 A, metal, fully shielded Mates with standard key 5-pin cordsets and receptacles</p>	<p>Female</p> <p>Male</p>
<p>CMBS 81..</p>				<p>Female</p> <p>Male</p>
<p>CMBS 82..</p>	<p>CMB 8181-0</p>	<p>CMBS 8181-0</p>	<p>Nickel Plated Brass, PG9 cable gland accepts 6-8 mm cable diameter, screw terminal accepts up to 18 AWG conductors, 85°C, 60 V, 2 A, metal, fully shielded, mates with standard key 8-pin cordsets and receptacles</p>	<p>Female</p> <p>Male</p>

Field Wireables