

8638PPS1005LF - D-Subminiature :
 Power Contacts 8638 Pin Solder
 Bucket 10A, >200 Cycles



www.fci.com

Specifications

Dimensional	
Length (Overall)	22.2 mm max
Size (Wire)	16 AWG
Strip length (Wire)	7 mm
Diameter A (Inner)	1.7 mm
Diameter B (outer)	2.6 mm
Electrical	
Current rating	10A
General	
Contact type	Power
Gender	Pin
Product Type	Contact
Termination Style	Solder Bucket
Mechanical	
Durability (Mating cycles)	Std Class (>200 Mating Cycles)
Other Features	
Most Popular Configuration	Yes
Category Path	Product type/Cable Assemblies and Cable Connectors/Cable Connectors/D-Subminiature/D-Subminiature Cable Signal and Power Product type/Cable Assemblies and IO cable connectors/IO cable connectors/D-Subminiature/D-Subminiature Cable Signal and Power Product type/Input-Output Connectors/D-Subminiature/D-Sub Cable Connectors
Physical	
Plating (Contact)	Gold over Nickel

Color (Clip)	Black
Plating (Termination)	Matte Tin over Nickel

