

8638PSC2005LF - D-Subminiature :
Power Contacts 8638 Socket Crimp
20A, >200 Cycles



www.fci.com

Specifications

Dimensional	
Length (Overall)	22 mm max
Size (Wire)	12 AWG - 14 AWG
Strip length (Wire)	7 mm
Diameter A (Inner)	2.8 mm
Diameter B (outer)	3.7 mm
Electrical	
Current rating	20A
General	
Contact type	Power
Gender	Socket
Product Type	Contact
Termination Style	Crimp
Mechanical	
Durability (Mating cycles)	Std Class (>200 Mating Cycles)
Other Features	
Most Popular Configuration	Yes
Category Path	Product type/Cable Assemblies and Cable Connectors/Cable Connectors/D-Subminiature/D-Subminiature Cable Signal and Power Product type/Cable Assemblies and IO cable connectors/IO cable connectors/D-Subminiature/D-Subminiature Cable Signal and Power Product type/Input-Output Connectors/D-Subminiature/D-Sub Cable Connectors
Physical	
Plating (Contact)	Gold over Nickel

Color (Clip)	Red
Plating (Termination)	Matte Tin over Nickel

