

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 16 MTW, MTW Cable



MTW Cable

TYPE MTW 90°C/TFF 60°C/AWM 105°C/VW-1 600 Volts

Stranded bare Copper, PVC Insulation

Ratings:

• **18 & 16 AWG:**

UL 600 Volts, 90°C MTW, 60°C TFF

105°C dry 60°C wet AWM (VW-1)

105°C & 90°C 1000 volts AWM

• **14, 12 & 10 AWG:**

UL 600 Volts, 90°C MTW, 60°C TW

105°C dry 60°C wet AWM(VW-1)

105°C & 90°C 1000 volts AWM

• **8 AWG:**

UL 600 Volts, 90°C MTW, 60°C TW

105°C dry 60°C wet, 105°C & 90°C

1000 volts AWM (VW-1)

• **6, 4 & 2 AWG:**

UL 600 Volts, 90°C MTW, 75°C THW

60°C oil resistant II, 105°C dry 60°C wet

105°C 1000 volts AWM (VW-1)

SPECIFICATIONS

Conductor Size	16 AWG
Stranding	26/.0100 Bare Copper
Insulation	PVC
Nom. Wall Thickness	0.030 in
Nom. O.D.	0.120 in
UL Style	1015 1032 1230 MTW
UL Rating	-20°C to +105°C, 600V, 1000 V
UL Flame Test	VW-1
CSA Type	TEW, TR-32
CSA Flame Test	FT-1

RoHS Compliant



RoHS Compliant