

Datasheet

RS Pro 5mm Pitch PCB Terminal Block with Screw Termination, Through Hole, 3 Way

RS Stock No: **494-9016**



Features and Benefits

- Rising clamp terminals for positive wire retention
- Accepts wires up to 2.5 mm²
- PBT construction

Specifications:

Colour	Grey
Current Rating	16 A
Depth	12.5 mm
Gender	Male
Length	15.6 mm
Material	PBT
Mounting Type	Through Hole



ENGLISH

Number of Contacts	3
Number of Rows	1
Pitch	5 mm
Termination Method	Screw
Type	PCB Terminal Block
Voltage Rating	250 V
Width	12.5 mm
Insulation Resistance	1000 mΩ
American Wire Gauge	12 to 26 AWG
Insulation Withstand Voltage	1500 V ac
Operating Temperature Range	-40 to +105°C
Flammability Rating	UL 94 V-1