

Datasheet

Stock No:

RS Pro Nylon 6.6 Snap Fit Clips



The RS Pro range of corrosion resistant Snap Fit nylon clips also known as Herbie Clip are available in a range of sizes from a 5.6mm minimum inside diameter to a 30.4mm maximum diameter.

Features & Benefits:

Can withstand pressure up to 200 psi

Working temperature -40°C to 130°C

Resistant to most solvents, petroleum products and common chemicals

Manufactured from UV stabilised material, therefore is resistant to ultra violet light and will not degrade in sunlight

Can easily be adjusted and reused after many years, even in corrosive environments

Resistant to most industrial solvents, petrol, oils, greases and many common chemicals

Typical Applications:

This product can be used in a wide range of applications when a hose or wire has to be secured. Used across many industries including marine, medical, food, automotive, electrical and white goods manufacturer and repair.

Standards:

Complies to BS EN ISO 9001:2000



Please view our full range listing below for all Nylon 6.6 Snap Fit Clips

Clip Type	Material	Grade	Inside Diameter Minimum	Inside Diameter Maximum	Part No.
Snap Fit Clip	Nylon	6.6	5.6 mm	6.5 mm	475-1415
Snap Fit Clip	Nylon	6.6	6.5 mm	8.1 mm	291-587
Snap Fit Clip	Nylon	6.6	7.9 mm	9.6 mm	291-593
Snap Fit Clip	Nylon	6.6	9.2 mm	10.8 mm	291-600
Snap Fit Clip	Nylon	6.6	10.2 mm	12.3 mm	291-616
Snap Fit Clip	Nylon	6.6	11.1 mm	13.4 mm	291-622
Snap Fit Clip	Nylon	6.6	12 mm	14.5 mm	291-638
Snap Fit Clip	Nylon	6.6	13.1 mm	15.7 mm	291-644
Snap Fit Clip	Nylon	6.6	15 mm	17.8 mm	291-650
Snap Fit Clip	Nylon	6.6	16.9 mm	19.9 mm	291-666
Snap Fit Clip	Nylon	6.6	18.1 mm	21.4 mm	291-672
Snap Fit Clip	Nylon	6.6	20.3 mm	23.7 mm	291-688
Snap Fit Clip	Nylon	6.6	22.2 mm	25.8 mm	291-694
Snap Fit Clip	Nylon	6.6	24.5 mm	28.4 mm	291-701
Snap Fit Clip	Nylon	6.6	26.5 mm	30.4 mm	291-717