

Blind sleeve - CES-SRG-BK - 0801670

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Small blind sleeve, material: NBR




Product description

Blind sleeves seal feed-through sections that are not required in CES sealing frames



Key commercial data

Packing unit	10 pc
GTIN	 4 046356 674768
Weight per Piece (excluding packing)	9.38 g
Custom tariff number	40169300
Country of origin	Taiwan

Technical data

Dimensions

Conductor sealing range	(Blind sleeve)
-------------------------	----------------

Ambient conditions

Degree of protection	IP54 (DIN IEC 60529)
	IP65 (when using a CES-B..SFFS-PLBK sealing frame with screw locking directly on the housing panel and a cable binder)
Ambient temperature (operation)	-40 °C ... 125 °C (static)

General

Product description	Blind sleeves seal feed-through sections that are not required in CES sealing frames
Material	NBR
Color	black

Blind sleeve - CES-SRG-BK - 0801670

Classifications

eCl@ss

eCl@ss 4.0	27081002
eCl@ss 4.1	27081002
eCl@ss 5.0	27081002
eCl@ss 5.1	27081002
eCl@ss 6.0	27081002
eCl@ss 7.0	27081002
eCl@ss 8.0	27081002

ETIM


ETIM 3.0	EC000879
ETIM 4.0	EC000451
ETIM 5.0	EC000451

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Drawings

Dimensioned drawing



Dimensional drawing