



Representative

Catalog Number: 54933BE
Product ID: 7TAH007900R0025
UPC Number: 78621019025
EAN Number: 05414363144540
Status: Active

Copper One-Hole Lug, Long Barrel, Blind End, Max 35kV, Wire Size #2 AWG, #10 Bolt Size, Tin Plated, Die Code 33, Die Color Code 33

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Long Barrel Copper Lug
Standard	UL E9809
Cable Size	#2 AWG
Stud Size	#10
Number Of Holes	1
Material	Copper
Color	Brown

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.25x2.75x2.25
Outer Quantity	50
Outer Dimensions (inches)	7.7x6.7x3.5
Weight Uom	4.38 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta01025-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com