

Cable binder base - WT-BASE LS HF 4 - 3240706

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable binder base, for cable binders up to 4 mm wide, self-adhesive (rubber) and screwable, 4 mm fixing hole, 4-sided cable binder feed-through



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
Weight per Piece (excluding packing)	0.712 g
Custom tariff number	39269097
Country of origin	Croatia

Technical data

Dimensions

Length (b)	19 mm
Width (a)	19 mm
Height	5 mm
Hole diameter	4.10 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (assembly)	-15 °C ... 40 °C

General

Color	transparent
Type	Fixing
Components	free from silicone and halogen
Flammability rating according to UL 94	HB
Material	ABS

Standards and Regulations

Order No.	3240706
Product key	BG413Z

Cable binder base - WT-BASE LS HF 4 - 3240706

Technical data

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Classifications

eCl@ss

eCl@ss 4.0	27140702
eCl@ss 4.1	27140702
eCl@ss 5.0	27140702
eCl@ss 5.1	27140702
eCl@ss 6.0	27140702
eCl@ss 7.0	27140702
eCl@ss 8.0	27140702

ETIM

ETIM 3.0	EC000046
ETIM 4.0	EC000046
ETIM 5.0	EC000046

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703