

Product Datasheet

[Catalog Home](#)[Home Page](#)[Search](#)

## SHC1024CR -- Cord Connectors



Nylon

Hubbell's nylon cord connectors resist most common industrial corrosive and provide effective pullout protection in a lightweight design. They are ideal for any application where weight, conductivity or corrosion may be an issue.

## Product Specifications

<b>Product Type</b>	Cord Connectors
<b>Material/Style</b>	Nylon Standard Style
<b>Cord Diameter Range</b>	.50"-.63" (12.7- 15.9)
<b>Cord Connector Body Style</b>	Straight Male
<b>Form Size</b>	F2
<b>HUB Size</b>	1/2"
<b>Color Code</b>	Brown
<b>Effective Operating Temperature</b>	-30°F to +225°F (-34°C to +107°C)
<b>Recommended Knockout Hole Size</b>	.86"-.91" (21.8-23.0)
<b>Flammability</b>	Hubbell nylon cord connectors have a UL 94-V2 rating.
<b>Hazardous Locations</b>	Hubbell cord connectors are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C. Reference 501-4(b), 502-4(a), 502-4(b), 503-3(a), and 503-3(b).
<b>Dimension A</b>	1.32" (33.5) Dia.
<b>Dimension B</b>	1.50" (38.1) Ref.
<b>Dimension C</b>	.53" (13.5)
<b>Dimension D</b>	.58" (14.7) Throat Dia.
<b>Dimension E A/C</b>	1.25" (31.7)
<b>Dimension E A/F</b>	1.12" (28.4)
<b>Certifications</b>	UL Listed in accordance with Standard 514B, CSA Certified, United States Coast Guard Approval, Title 46-Part 111.
<b>UPC Number</b>	78358520806
<b>Weight in LBs</b>	0.15
<b>Link to Drawing Library</b>	<a href="#">Click here for Library</a>
<b>Link to PDF Catalog</b>	<a href="#">Click here for Catalog</a>

