




## PRODUCT DATA

### Thermocouple Extension & Compensating Cable

### PVC Insulated Flat Pair (to IEC-584)



- PVC insulated flat pair construction
- Conductors laid flat PVC insulated with overall PVC sheath
- All round general purpose cable, both waterproof and very flexible
- Thermocouple extension types for K, J, T & N
- Compensating types VX (KCB) & U (RCA) for types K & R/S Thermocouples respectively
- Stranded conductors available, either 7/0.2mm or 13/0.2mm
- Available in 10, 25 & 100 metre lengths
- Tolerance Class 2
- Insulation rating -10°C to 105°C
- Colour code (cores & jacket) to IEC-584-3

T/C Type	Conductors	Cores	Jacket	Reel Length	RS order code
<b>Extension:</b>					
KX	7/0.2mm	+Green/-White	Green	25 metres	236-3820
KX	7/0.2mm	+Green/-White	Green	100 metres	611-7889
JX	7/0.2mm	+Black/-White	Black	10 metres	219-4753
JX	7/0.2mm	+Black/-White	Black	100 metres	236-3915
TX	7/0.2mm	+Brown/-White	Brown	10 metres	219-4703
TX	7/0.2mm	+Brown/-White	Brown	25 metres	236-3870
TX	7/0.2mm	+Brown/-White	Brown	100 metres	762-1146
NX	7/0.2mm	+Pink/-White	Pink	10 metres	219-4668
<b>Compensating:</b>					
VX (KCB)	7/0.2mm	+Green/-White	Green	25 metres	219-4551
VX (KCB)	7/0.2mm	+Green/-White	Green	100 metres	219-4573
VX (KCB)	13/0.2mm	+Green/-White	Green	100 metres	762-1152
U (RCA)	7/0.2mm	+Orange/-White	Orange	25 metres	611-7902
U (RCA)	13/0.2mm	+Orange/-White	Orange	10 metres	219-4769