

For Patient-Care Vicinity – UL 1363A Medical-Grade Power Strip; 4 Hospital-Grade Outlets, 10 ft. Cord, Drip Shield, Cord

MODEL NUMBER: PS410HGOEMX



Description

The PS410HGOEMX Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets.

Two built-in resettable 15A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The built-in cord wrap provides easy cord management in mobile applications. The drip shield can be mounted for extra protection when there are liquids in the environment.

Mounting tabs and flanges let you install the PS410HGOEMX on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. The all-metal housing ensures safety and is guaranteed to last a long time in demanding surroundings.

Features

Power Distribution Anywhere in Any Medical Facility

- Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas
- For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted
- 120V, 50/60 Hz power strip complies with UL 1363A specifications

Versatile Medical-Grade Solution

Highlights

- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A specifications
- 10 ft. cord with NEMA 5-15P-HG hospital-grade plug
- Features 4 NEMA 5-15R-HG hospital-grade outlets
- Optional drip shield provides extra protection from liquids

Package Includes

- PS410HGOEMX UL 1363A Medical-Grade Power Strip with four 15A Hospital-Grade Outlets, 10 ft. Cord, Cord Wrap and Drip Shield
- Owner's Manual with maintenance requirements



- 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power
- Integrated cord wrap provides easy cord management
- Rugged, all-metal housing for long life in demanding environments

Premium Safety Features

- Dual, resettable built-in 15A circuit breakers protect against dangerous overloads
- Switchless design prevents accidental shut-off
- Drip shield adds extra measure of safety against liquids and moisture

Ready to Use Right Out of the Box

- Built-in mounting tabs and flanges make the PS410HGOEMX easy to install on a variety of surfaces

Specifications

MODEL TEXT	
Key Benefit	Power strip with built-in cord manager and optional drip shield supplies power to movable plug-connected components mounted to IV poles, carts and mobile medical workstations inside or outside of patient-care vicinities.
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Outlet Orientation	Single row of 4
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Connection Type	NEMA 5-15P-HG
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Shipping Dimensions (hwd / in.)	10.12 x 6.10 x 2.36
Shipping Dimensions (hwd / cm)	25.70 x 15.49 x 5.99
Shipping Weight (lbs.)	3.06
Shipping Weight (kg)	1.39
Unit Dimensions (hwd / in.)	9.94 x 4.28 x 2.17
Unit Dimensions (hwd / cm)	25.25 x 10.8712 x 5.51
Unit Weight (lbs.)	2.84
Unit Weight (kg)	1.29
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs and flanges enable mounting to a variety of surfaces
Receptacle Color	White
Color (AC Line Cord)	White
CERTIFICATIONS	
Approvals	TUV tested to UL 1363A
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>