


REV	DESCRIPTION\PER REQUEST	DRAWN	DATE



10	Shell	1	Brass	Nickel
9	Gasket	1	Rubber	Red
8	Retaining ring	1	SK-5	Nickel
7	Dielectric	1	Delrin	None
6	Washer	1	Brass	Nickel
5	Dielectric	1	Teflon	None
4	Dielectric	1	Teflon	None
3	Pin	1	Phos Bronze	Gold
2	Body	1	Brass	Nickel
1	Body	1	Brass	Nickel
<i>NO</i>	<i>Description</i>	<i>Q'ty</i>	<i>Material</i>	<i>Finish</i>

PART NO. 531RP9505		* MAJOR DIMENSION		Bomar Interconnect Products, Inc	
APPROVED		UNLESS OTHERWISE NOTED TOLERANCES			
DATE 10/30/12		0.5-6=±0.2		TITLE	
CHECKED		6-30=±0.4		SMA JACK TO TNC R/P PLUG ADAPTER	
DATE 10/30/12		30-120=±0.6		DRAWING NO.	
DRAWN		120-315=±1.0		ASSMA-10153-1-RP-TGN	
DATE 10/30/12		ANGLES=±1°		REV A	
Wen		SCALE 4/1	UNIT mm	FILE NO. W:\AS\ASSMA\ASSMA-10153-1-RP-TGN Bomar->20121105	