

Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 374, UL1061 Wire



UL1061 Wire

Stranded Tinned Copper, Color Coded, Semi-Rigid PVC Insulation

Characteristics:

Temperature Rating — 10°C to +80°C, 300 volts in business machine or electronic computers only.

Applications:

Internal wiring of computers, electric book-keeping, accounting machines, and other office and control equipment.

SPECIFICATIONS

Conductor Size	20 AWG
Stranding	7/28 Tinned Copper
Insulation	Semi Rigid PVC
Nom. Wall Thickness	0.009 in
Nom. O.D.	0.057 in
UL Style	1061
UL Rating	-10°C to +80°C, 300 V
UL Flame Test	VW-1
CSA Type	AWM
CSA Flame Test	FT-1
RoHS Compliant	 RoHS Compliant
Color Code	Hook Up Wire Color Code Chart