

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0430310003](#)
Status: **Active**
Overview: Micro-Fit 3.0 Connector System Product Family
Description: Micro-Fit 3.0 Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel

Documents:

Drawing (PDF)	Product Specification TS-46235-001-001 (PDF)
Product Specification PS-43045 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-43045-001 (PDF)	Product Literature (PDF)
Product Specification TS-43045-002-001 (PDF)	



General

Product Family	Crimp Terminals
Series	43031
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Micro-Fit 3.0 Connector System Product Family
Packaging Alternative	43031-0009 (Loose)
Product Literature Order No	987650-5984
Product Name	Micro-Fit 3.0
UPC	800754369435

Physical

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.061/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	20, 22, 24
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	8.5A
-------------------------------	------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Product Specification	PS-43045, PS-43045-001, TS-43045-002-001, TS-46235-001-001
Sales Drawing	SD-43031-XXXX

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[43031 Series](#)

Use With

Micro-Fit 3.0 Plug Housings [43020](#) , [43640](#)

Micro-Fit BMI Plug Housings [44300](#) , [46625](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

Extraction Tool	11030043
-----------------	--------------------------

Insertion Tool for	638120800
--------------------	---------------------------

Micro-Fit 3.0 and

CRC Male and

Female Crimp

Terminals, 20-30

AWG

Hand Crimp Tool	638190000
-----------------	---------------------------

FineAdjust Applicator	<u>639004500</u>
for Insulation OD	
1.30-1.85mm, 20-24	
AWG Wire	
FineAdjust Applicator	<u>639018800</u>
for Insulation OD	
1.10-1.30mm - 20-24	
AWG	
FineAdjust Applicator	<u>639018900</u>
for Insulation OD	
0.91-1.09mm - 20-24	
AWG	
T2 Terminator	<u>639104500</u>
for Insulation OD	
1.30-1.85mm, 20-24	
AWG	
T2 Terminator	<u>639118800</u>
for insulation OD	
1.10-1.30mm - 20-24	
AWG	
T2 Terminator	<u>639118900</u>
for insulation OD	
0.91-1.09mm - 20-24	
AWG	
Japan	
Description	Product #
S-1 Applicator for	<u>572983700</u>
Micro-Fit 3.0 Plug	
and Receptacle	
Crimp Terminals,	
20-24 AWG	

This document was generated on 11/28/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION