

You are here: Home > Products > Power Distribution > Rack-mount Transfer Switches

## **Rack-mount Transfer Switches**

Rack ATS, 100-120V, 15A, 5-15P In, (10) 5-15R Out

APC Rack-mount Transfer Switches, Input: 100V, 120V, Input Connections: NEMA 5-15P, Cord Length:8 feet ( 2.44 meters ), Output: 100V, 120V, Output Connections: NEMA 5-15R

AP7750A

Printer Friendly

**Email Technical Specifications** 

Includes: Rack Mounting brackets, User Manual

Standard Lead Time: Usually in Stock



> Wall-mount Transfer Switches

Room Power Distribution (1)

Transfer Switches

> Rack-mount Transfer Switches

Return to Power Distribution



Technical Specifications Product Overview Documentation Software & Firmware Options

Output		
Output Nominal Output Voltage	100V, 120V	
Maximum Total Current Draw per Phase	15A	
Output Connections	(10) NEMA 5-15R	
Input		
Nominal Input Voltage	100V, 120V	
Input Frequency	50/60 Hz	
Regulatory Derated Input Current (North America)	12A	
Input Connections	NEMA 5-15P	$\left( \begin{smallmatrix} \nabla \\ 0 \end{smallmatrix} \right)$
Cord Length	2.44 meters	
Number of Power Cords	2	
Acceptable Input Voltage	100-125 VAC	
Maximum Input Current per phase	15A	
Load Capacity	1440 VA	
Physical		
Net Weight	4.70 KG	
Maximum Height	44.00 mm	
Maximum Width	432.00 mm	
Maximum Depth	236.00 mm	
Shipping Weight	6.48 KG	
Shipping Height	114.00 mm	
Shipping Width	600.00 mm	
Shipping Depth	356.00 mm	

Color	Black	
Environmental		
Operating Environment	-5 - 45 °C	
Operating Relative Humidity	0 - 95%	
Operating Elevation	0-3000 meters	
Storage Temperature	-25 - 65 °C	
Storage Relative Humidity	0 - 95%	
Storage Elevation	0-15000 meters	
Conformance		
Regulatory Approvals	FCC Part 15 Class A, ICES-003, TUV-C, TUV-NURTL, VCCI Class A	
Standard Warranty	2 years repair or replace	
Sustainable Offer Status		
RoHS	Compliant	
REACH	REACH: Contains No SVHCs	
Battery Directive	Compliant	
Battery Notes	Contains Lithium Battery	

©APC by Schneider Electric