



DW340K Features

- Durable hot air gun for professional continuous operation
- 2000 Watt power with optimised cooling
- Compact and lightweight for easy handling in use
- Safe, stand-free, use for numerous tasks thanks to stable stationary positions and rubber insert
- Variable temperature control and regulation, for versatile use even in continuous operation, always suited to the material being worked on

DW340K Specifications

Specifications

Specifications	Value
Power Input	2000 Watts
Operating Temperature	50-600 °C
Air Flow	650 l/min
Weight	0.85 kg
Length	265 mm
Height	210 mm
Hand/Arm Vibration	2.5 m/s ²
Uncertainty K 1 (Vibration)	1.5 m/s ²
Sound Pressure	75 dB(A)
Acoustic Pressure	88 dB(A)

DW340K Standard

- Glass protection nozzle
- Spoon reflector nozzle

- Cone nozzle
- Fish tail surface nozzle
- Steel paint scraper for all applications

