

## Sensor/Actuator cable - SAC-8P-MR/ 2,0-542 SCO BK - 1406102


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/Actuator cable, 8-position, PVC, yellow, Plug angled M12-SPEEDCON, A-coded, on Free cable end, Cable length: 2 m



### Key commercial data

|                      |   |
|----------------------|---|
| Packing unit         | 1 PCE   |
| GTIN                 | <br>4 046356 799478 |
| Custom tariff number | 85444290  |
| Country of origin    | UNITED STATES   |

### Technical data

#### Dimensions

|                 |     |
|-----------------|-----|
| Length of cable | 2 m |
|-----------------|-----|

#### Ambient conditions

|                                 |                                  |
|---------------------------------|----------------------------------|
| Ambient temperature (operation) | -25 °C ... 90 °C (Plug / socket) |
| Degree of protection            | IP65                             |
|                                 | IP67                             |
|                                 | IP68                             |

#### General

|                       |                                       |
|-----------------------|---------------------------------------|
| Rated current at 40°C | 2 A                                   |
| Rated voltage         | 30 V                                  |
| Number of positions   | 8                                     |
| Contact resistance    | ≤ 5 mΩ                                |
| Insulation resistance | ≥ 100 MΩ                              |
| Standards/regulations | M12 plug-in connector IEC 61076-2-101 |

## Sensor/Actuator cable - SAC-8P-MR/ 2,0-542 SCO BK - 1406102

### Technical data

#### General

|                             |   |
|-----------------------------|---|
| Coding                      | A - standard                                |
| Surge voltage category      | II  |
| Pollution degree            | 3   |
| Insertion/withdrawal cycles | ≥ 100                                       |
| Torque                      | 0.4 Nm (M12 plug-in connector)              |
| Contact material            | CuZn  |
| Contact surface material    | Ni/Au                                       |
| Contact carrier material    | TPU GF                                      |
| Material of grip body       | TPU, hardly inflammable, self-extinguishing |
| Material, knurls            | Zinc die-cast, nickel-plated                |
| Status display              | No  |

#### Line characteristics

|   |  |
|---|--|
| Cable type                                    | PVC yellow 105 °C                                  |
| Cable type (abbreviation)                     | 542  |
| UL AWM style                                  | 2517 (105°C/300 V)                                 |
| AWG signal line                               | 24   |
| Core diameter including insulation            | 1.12 mm ±0.03 mm                                   |
| Wire colors                                   | white, brown, green, yellow, gray, pink, blue, red |
| Overall twist                                 | 8 wires around filler to the core                  |
| External sheath, color                        | yellow   |
| External cable diameter D                     | 5.7 mm ± 0.2 mm                                    |
| Minimum bending radius, flexible installation | 8 x D  |
| Cable weight                                  | 44 kg/km   |
| Outer sheath, material                        | PVC  |
| Material, filler                              | PP   |
| Material conductor insulation                 | PVC  |
| Conductor material                            | Tin-plated Cu litz wires                           |
| Nominal voltage, cabel                        | 300 V  |
| Other resistance                              | UV resistant                                       |
| Ambient temperature (operation)               | -30 °C ... 105 °C (cable, fixed installation)      |

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001855 |
| ETIM 4.0 | EC001855 |
| ETIM 5.0 | EC001855 |

# Sensor/Actuator cable - SAC-8P-MR/ 2,0-542 SCO BK - 1406102

## Classifications

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 11     | 31251501 |
| UNSPSC 12.01  | 31251501 |
| UNSPSC 13.2   | 31251501 |
| UNSPSC 6.01   | 31251501 |
| UNSPSC 7.0901 | 31251501 |

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27060306 |
| eCl@ss 4.1 | 27060306 |
| eCl@ss 5.0 | 27061801 |
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 27061801 |
| eCl@ss 7.0 | 27061801 |

## Approvals

### Approvals

---

#### Approvals

UL Listed / cUL Listed / cULus Listed

---


#### Ex Approvals

---

#### Approvals submitted

---

## Approval details

|   |      |
|---|------|
| UL Listed  |      |
| Nominal current IN  | 2 A  |
| Nominal voltage UN  | 30 V |

# Sensor/Actuator cable - SAC-8P-MR/ 2,0-542 SCO BK - 1406102

## Approvals

|                    |      |
|--------------------|------|
| cUL Listed         |      |
| Nominal current IN | 2 A  |
| Nominal voltage UN | 30 V |

|              |  |
|--------------|--|
| cULus Listed |  |
|--------------|--|

## Accessories

### Accessories

#### Fuse

Fuse clip - SAC-M12-EXCLIP-M - 1558988



Fuse clip for the pin side of various M12 sensor/actuator connectors prevents plug-in connections being interrupted without using a tool

## Marking

Insert label - PABA WH/15 - 1013151



Insert label, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Thread on, Cable diameter: 0.6-50 mm, Lettering field: 15 x 4 mm

Insert label - PABA YE/15 - 1013698



Insert label, Strip, yellow, Unlabeled, Can be labeled with: Plotter, Mounting type: Thread on, Cable diameter: 0.6-50 mm, Lettering field: 15 x 4 mm

## Sensor/Actuator cable - SAC-8P-MR/ 2,0-542 SCO BK - 1406102

### Accessories

Insert label - PABA RD/15 - 1013944



Insert label, Strip, red, Unlabeled, Can be labeled with: Plotter, Mounting type: Thread on, Cable diameter: 0.6-50 mm, Lettering field: 15 x 4 mm

---

Conductor marker carrier - PATG 2/15 - 1013038



Conductor marker carrier, transparent, Unlabeled, Mounting type: Slide on, Cable diameter: 2-4 mm, Lettering field: 4 x 15 mm

---

Conductor marker carrier - PATG 3/15 - 1013041



Conductor marker carrier, transparent, Unlabeled, Mounting type: Slide on, Cable diameter: 4-7 mm, Lettering field: 4 x 15 mm

---

Conductor marker carrier - PATG 4/15 - 1013054



Conductor marker carrier, transparent, Unlabeled, Mounting type: Slide on, Cable diameter: 6-10 mm, Lettering field: 4 x 15 mm

---

Marker pen - B-STIFT - 1051993



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm

---

### Protection and sealing elements

## Sensor/Actuator cable - SAC-8P-MR/ 2,0-542 SCO BK - 1406102

### Accessories

Sealing cap - PROT-M12 FS-PA-CHAIN - 1430873

M12 sealing cap made of plastic with fixing band, for sensor cables, for free M12 sockets



---

### Tools

Cable-cutting tool - CUTFOX-S VDE - 1212207



Diagonal cutter for copper and aluminum conductors, VDE-tested

---

Stripping tool - WIREFOX SAC - 1212623



Stripping pliers, for halogen-free sensor/actuator cables (SAC cables), with PUR and PVC insulation, from  $\varnothing$  of 4.4 to 7 mm, any stripping length

---

Stripping tool - WIREFOX 10 - 1212150



Stripping tool, for cables and conductors from 0.02 - 10 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade

---

Torque screwdriver - TSD 04 SAC - 1208429



Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors

# Sensor/Actuator cable - SAC-8P-MR/ 2,0-542 SCO BK - 1406102

## Accessories

Torque screwdriver - TSD-M 1,2NM - 1212224



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm

Adapter insert - TSD-M SAC-BIT ADAPTER - 1212600



Adapter bit for TSD-M...torque tools, E6.3-1/4" drive with 4 mm hexagon to accommodate SAC bits


Tool - SAC BIT M12-D15 - 1208432



Nut for assembling sensor/actuator cables with M12 connector and for M12 connectors with QUICKON fast connection technology, for 4 mm hexagonal drive


## Drawings

Schematic diagram



Pin assignment M12 plug, 8-pos., view plug side


Dimensioned drawing



M12 x 1 male plug, angled

## Sensor/Actuator cable - SAC-8P-MR/ 2,0-542 SCO BK - 1406102

Circuit diagram



Contact assignment of the M12 plug