## SZR-MY4-N1-AC110-120V

( Home : Products : basics : Switches : Relays : SZR-MY )



SZR-MY General Purpose Relay: LED Indicator; Plug-in/Solder Terminal; 4PDT; 110/120 Vac

Actual product appearance may vary.

| P                                    | roduct Specifications                        |
|--------------------------------------|--|
| Current Rating                       | 3 A  |
| Contact(s)                           | 4PDT   |
| Terminal                             | Solder/Plug-In                               |
| Options                              | LED Indicator                                |
| Resistive Load                       | 220 V, 3 A                                   |
| Inductive Load                       | 220 V, 1.5 A                                 |
| Sw itching (Resistive Load)          | 660 VA                                       |
| Sw itching (Inductive Load)          | 176 VA                                       |
| Contact Rating                       | 250 Vac                                      |
| Coil Input Voltage                   | 110/120 Vac                                  |
| Rated Current at 50 Hz               | 9.9 mA/10.8 mA                               |
| Rated Current at 60 Hz               | 8.4 mA/9.2 mA                                |
| Coil Resistance                      | 4430 ohms                                    |
| Pow er Consumption                   | 0.9 W to 1.1 W                               |
| Dropout Voltage (% of Rated Voltage) | 30 % min.                                    |
| Pick-Up Voltage (Must Operate)       | 80 % max. of the Rated Coil Voltage          |
| Voltage                              | 110 % of the rated coil voltage              |
| Operating Voltage                    | 80 % of the rated coil voltage               |
| Operate Time                         | 20 ms max.                                   |
| Release Time                         | 20 ms max.                                   |
| Ambient Temperature                  | -25 °C to 75 °C [-13 °F to 167 °F]           |
| Ambient Humidity                     | 45 % RH to 85 % RH                           |
| Contact Material                     | Gold-Plated Silver                           |
| Contact Resistance                   | 50 mOhm max.                                 |
| Operating Frequency (Mechanical)     | 18,000 Operations/Hour                       |
| Operating Frequency (曰ectrical)      | 1800 Operations/Hour                         |
| Vibration Resistance                 | 10 Hz to 55 Hz at Double Amplitude of 1.0 mm |
| Shock Resistance                     | 1000 m/s2 (Approx. 100 G)                    |
| Weight                               | 35 g [1.24 oz]                               |

| Product Specifications         |                                     |  |
|--------------------------------|-------------------------------------|--|
| Agency Approvals and Standards | UL, CE                              |  |
| UL File#                       | E#150950                            |  |
| Expected Mechanical Life       | ac - 50 Million Operations min.     |  |
| Comment                        | LED Indicator; Solder/Plug-in; 4PDT |  |
| Availability                   | Global                              |  |
| Series Name                    | SZR-MY                              |  |