

Jonard New Products

OK Industries Wire Wrap Tools

Pliers [▶](#)

Wrenches & Nut Drivers [▶](#)

Fiber Optic Products [▶](#)

CATV / Satellite Tools [▶](#)

Screwdrivers [▶](#)

Telecommunication Tools [▶](#)

Electrical Tools [▶](#)

Security & Alarm [▶](#)

Wire & Cable Strippers [▶](#)

Cable Installation (Fishing) [▶](#)

Punchdown Tools [▶](#)

Insulated Tools [▶](#)

Kynar Wire [▶](#)

Connector Tools [▶](#)

Solder and Desolder [▶](#)

IC Insertion and Extraction Tools [▶](#)

Force Gauges [▶](#)

Burnishers [▶](#)

Alignment Tools [▶](#)

Wire Wrapping Tools - Jonard [▶](#)

[New Products ▶](#)

[Product Index ▶](#)

[Download Product Catalog ▶](#)

[Newsletter](#) |

[Print](#) |

[Share](#) |

[Share](#) |

[Email](#)



[VIEW LARGER IMAGE >>](#)

## Adjustable Wrenches - AW Series

All wrenches are made of chrome vanadium steel with a chrome plated finish.

Wrenches are forged and heat treated for greater strength. Handles are covered with a red transparent plastic for user comfort. The knurl is precision formed and the operation is smooth and trouble free. For accurate adjustments use the metric or English scales on either side of the jaws.

Part No.	Description	Length	Jaw Capacity	Weight
AW-6	Adjustable Wrench 6"	6" (152 mm)	15/16" (24mm)	5.2 oz
AW-8	Adjustable Wrench 8"	8" (203mm)	1 1/8" (29mm)	10.6 oz
AW-10	Adjustable Wrench 10"	10" (254mm)	1 5/16" (33mm)	14.6 oz
AW-12	Adjustable Wrench 12"	12" (305 mm)	1 1/2" (38mm)	24 oz