

Datasheet

Expansion Inserts





- Nickel plated brass insert
- Use in drilled or moulded-in holes
- Install by simple press or hammer-in methods
- Available with flush head, or flange head

Stock No.	Material	Finish	Thread Size	-	Body Outside Diameter	Body Depth		Mounting Type
278-534	Brass	Nickel Plated	M3	4 mm	4.22 mm	4.78 mm	6.7 mm	Flush
278-540	Brass	Nickel Plated	M3.5	4.8 mm	5.06 mm	6.35 mm	8.4 mm	Flush
278-556	Brass	Nickel Plated	M4	5.6 mm	5.64 mm	7.95 mm	10.2 mm	Flush
278-562	Brass	Nickel Plated	M5	6.4 mm	6.65 mm	9.35 mm	12.2 mm	Flush
278-578	Brass	Nickel Plated	M6	8 mm	8.26 mm	12.7 mm	16 mm	Flush
278-584	Brass	Nickel Plated	M3	4 mm	4.22 mm	4.78 mm	6.2 mm	Flange
278-590	Brass	Nickel Plated	M3.5	4.8 mm	5.06 mm	6.35 mm	7.8 mm	Flange
278-607	Brass	Nickel Plated	M4	5.6 mm	5.64 mm	7.95 mm	9.4 mm	Flange
278-613	Brass	Nickel Plated	M5	6.4 mm	6.65 mm	9.53 mm	11.2 mm	Flange
278-629	Brass	Nickel Plated	M6	8 mm	8.26 mm	12.7 mm	14.8 mm	Flange

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.