







ES-246 ETHERNET TO SERIAL DEVICE SERVER Ethernet 1 Port RS232

CONNECT, CONFIGURE, CONTROL YOUR SERIAL DEVICES



Features

- 1 port RS232
- Max baud rate 1,000,000 1 MegaBaud
- 10/100Base TX Ethernet port
- User friendly interface, simple to use, powerful in operation
- Web configuration and RFC2217 compliant interface for non-Windows users
- IP-30 rated enclosure
- LED status indication
- Optional DIN rail mounting kit
- Serial Port Tunneling (individually configurable) allows serial cable replacement over any distance, no software required
- Power supply included (power input 5-30V DC)
- Simple operation for each and every operating system!

Description

Ethernet to Serial device server providing access to one RS232 serial port. Data transfer rates up to 1,000,000 baud, coupled with 1Mbit/s line drivers deliver uncompromising performance. Our ES range provides simple instant networked serial ports. A web interface allows secure configuration and control of the serial ports over a local network or the internet using any browser. For Windows our in-house designed 32 bit and 64 bit driver gives you local COM ports, retaining existing software applications and allowing you to connect across your network to remote devices just as if they were attached locally. Serial Port Tunnelling individually configurable allows serial cable replacement over any distance, no software required. You can access the device via TCP/IP sockets from any networked device like an Android tablet, PC or phone. On Windows OS TCP/IP sockets are handled by the Winsock API, this will differ on other OSs.

Windows Users - Our software drivers gives you local COM ports, allowing you to retain your existing software applications and connect to your devices over the network. COM Port can be assigned from COM1 to COM255 and the Brainboxes Ethernet to serial device remembers your COM Port assignment on reboots.

Web Interface Users (Linux/Apple OS/Android) - Alternatively access the device via TCP/IP socket from any networked device. Configure options via web interface.


Extend your reach! Remote serial devices with local control. With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

Example Application





Box Information



LED I	ntorm	ation
-------	-------	-------

Status LED	Green	Device Ready
	Flashing Yellow	Changing Settings
	Flashing between Red & Green	Querying IP
	Flashing Green/Red	User performing Hard Reset
	Flashing between Green & Red/Yellow	IP address diagnostic
	Flashing between Green & Yellow	Initialization diagnostic
Serial Port LEDs	Green light on	Port Open
	Flashing Green	Data RX / TX
Network LED	Green light on	Link Established
	Flashing Green	Data RX / TX

Port

Ports 1 port RS232

Connector DB9 Connector - 9 Pin Male

Power Input 5 - 30V DC input, reverse polarity protected

Power Consumption 0.76W Typical

ES-246 Ethernet 1 Port RS232



Port Settings - RS232

Baud Rate From 110 - 1,000,000 1 MegaBaud

Data Bits 5,6,7 or 8

Parity Odd, Even, None, Mark or Space

Stop Bits 1 or 2

Flow Control RTS/CTS, DSR/DTR, XON/XOFF

Tx/Rx Modes Point to Point

Port Settings - Ethernet

Data Rate 10/100 Mega bits/second

Cabling Normal / Crossover auto-sensing (Auto-MDIX)

Environmental

Operating Temperature 0 to 55°c **Storage Temperature** -20 to 85°c

Ambient Relative Humidity 5 to 95% (non-condensing)

Housing IP-30 rated case

Software

Network Protocols ICMP, IP, TCP, UDP, DHCP, BOOTP, Telnet, HTTP, RFC2217

Data Transfer Protocol TCF

Configuration Options Windows Utility, Web Interface

OS Compatibility
Microsoft Windows 8 32 bit 64 bit Editions / Microsoft Windows 7 32 bit 64 bit Editions / Windows Server 2008 32 bit 64 bit Editions / Windows Vista 32 bit 64 bit Editions / Windows Server 2003 32 bit 64 bit Editions / Windows Vista 32 bit 64 bit Editions / Windows Server 2003 32 bit 64 bit Editions / Windows Vista 32 bit 64 bit Editions / Windows Server 2003 32 bit 64 bit Editions / Windows Vista 32 bit 64 bit Editions / Windows Server 2003 32 bit 6

tions / Windows XP 32 bit 64 bit Editions / Fully RFC2217 compliant / Interface for other OS's & Linux

Approvals

Industry Approvals AEO C-TPAT Microsoft Certified Gold Partner WEEE RoHS EMC: CE TAA

Microsoft ApprovalsMicrosoft Certified Gold PartnerMicrosoft Signed DriversWindows 7 32 bit 64 bit Editions















Packing Information

Packaging Quick Start Guide, Country Specific Power Supply, Installation CD including manual, Microsoft signed drivers

& utilities

Device Ethernet 1 Port RS232

Accessory Items Global Power Supply - PW-800 (included), DIN-Rail Mounting Kit - MK-048

Packaged Weight 0.362 kg

Packaged Dims 200l x 135w x 80h mm

ES-246 Ethernet 1 Port RS232



Product Support

Warranty Lifetime - online registration required

Support Lifetime Web, Email and Phone Support from fully qualified, friendly staff who

work in and alongside the Product Development Team



Additional Information

OEM option Available for bulk buy OEM

Made In Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards

'Manufacturer of the Year'

Customisable Brainboxes operate a 'Perfect Fit Custom Design' policy for volume users. More info:

sales@brainboxes.com

Accessory Items

ORDER CODE - DIN-Rail Mounting Kit - MK-048



ORDER CODE - Additional Global Power Supply - PW-800

