
SP6MAWT 6.5" speaker

Features

Speco Technologies' Multi-Application Series was designed to make the contractor's work as easy and time-efficient as possible.

Our all-in-one unit comes pre-assembled with back can and mounted transformer. It features a quick-flip 70 or 25 Volt selector switch and an easy-select transformer wattage dial. The 8 individual wattage tap settings cover a complete range of uses. This flame-retardant ABS unit also comes with insulated wires and built-in easy mount tabs for securing the unit. The MA Series is the ideal, all-purpose value speaker covering a wide range of commercial applications. The furnished 8 Ohm tap selector also means the speakers can be kept on-hand for unexpected residential installation needs.

Specifications

Frequency Response: 50Hz – 20kHz

Woofer: 6.5" Fiberglass with rubber surround

Tweeter: 1" Titanium, pivoting

Sensitivity: 89±3dB

Impedance: 8 Ohms

RMS Power: 40W

Max. Power: 80W

Transformer: Selectable 70/25V (40W, 30W, 15W,
7.5W, 5W, 2.5W, 1W, 0.5W, & 8 Ohms)

Minimum Mounting Depth: 4.13"

Mounting Dimensions: 7.5" (W) x 10.75" (H)

Dimensions: 8.63" (W) x 12" (H) x 4.25" (D)

Weight: 5.5 lbs.



sold individually