

SIEMENS

Product data sheet

6SE6400-3CC00-4AD3



Fig. similar

MICROMASTER 4 AC COMMUTATION CHOKE 200V
-480V 3AC 3,5A FOOTPRINT FSA - 3X3.9MH NOT
FOOTPRINT FOR V20

Output current / rated value	3.5 A
Effective power loss	
• at 50 Hz	12.5 W
• at 60 Hz	15 W
Connectable conductor cross-section	
• for line supply conductor	6 mm ²
• for load-side outgoing feeder	1.5 mm ²
Design of electrical connection / for PE conductor	M5 stud bolt
Protection class IP	IP20
Width	75.5 mm
Height	201 mm
Depth	50 mm
Net weight	1.3 kg

Further information

[Information and download center for Industry Automation and Drives](#)

[Technical documentation \(Motion Control\)](#)

[Industry Mall \(online ordering system\)](#)

[Service & Support \(FAQs, manuals, operating instructions, certificates, characteristics, ...\)](#)

last change:

Mar 1, 2013