


































# Flexible LED Strip Accessories

	NTE Type No.	Description
<b>Power Supplies and Dimmers</b>		
	LEDTA-6	Power Supply, 12V, 2A, 24W, 2.1mm x 5.5mm plug
	69-D24	Power Supply, 12V, 2A, 24W, 2.1mm x 5.5mm plug
	69-D36	Power Supply, 12V, 3A, 36W, 2.1mm x 5.5mm plug
	69-D48	Power Supply, 12V, 4A, 48W, 2.1mm x 5.5mm plug
	69-D72	Power Supply, 12V, 6A, 72W, 2.1mm x 5.5mm plug
	57-12D-8000-4	Power Supply, 12V, 8A, 96W, 2.1mm x 5.5mm plug
	57-12D-10000-4	Power Supply, 12V, 10A, 120W, 2.1mm x 5.5mm plug
	69-DIM1	LED Dimmer, RF, Remote Controlled, 12V, 8A, 96W for Single Color LED Strips. For use with up to four 24 watt, two 36 watt, two 48 watt, or one 72 watt LED Strip(s). Contains 1 remote and 1 dimmer.
	69-DIM2	LED Dimmer, Knob Operated Control, 12V, 8A, 96W for Single Color LED Strips. For use with up to four 24 watt, two 36 watt, two 48 watt, or one 72 watt LED Strip(s).
<b>Remote Controls</b>		
	69-RTC1	Remote Control and Receiver for Red/Green/Blue flexible LED strips. Soft touch solid gradual hopping modes color ring. Contains 1 remote and 1 receiver.
	69-RTC10	Remote Control and Receiver for Red/Green/Blue + White and Red/Green/Blue + Warm White flexible LED strips. Soft touch buttons and color ring, 15 predefined pattern modes. Contains 1 remote and 1 receiver.
<b>Connectors</b>		
	69-A1	Female DC Connector with 5.75 inch leads, 5.5mm x 2.1mm for power supplies and remote receiver
	69-A2	3528 Size LED Connector with 5.75 inch leads – Add to cut strips <b>* For 300 LEDs per Reel ONLY</b>
	69-A3	5050 Size LED Solid Color Connector with 5.75 inch leads – Add to cut strips
	69-A4	5050 Size LED Red/Green/Blue Connector with 5.75 inch leads – Add to cut strips
	69-A5	3528 Size LED Solid Color Connector – For joining strips <b>* For 300 LEDs per Reel ONLY</b>
	69-A6	5050 Size LED Solid Color Connector – For joining strips
	69-A7	5050 Size LED Red/Green/Blue Connector – For joining strips

# Flexible LED Strip Accessories (Cont'd)

	NTE Type No.	Description
<b>Connectors (Cont'd)</b>		
	69-A8	Waterproof 3528 and 5050 Size LED Solid Color Connector
	69-A9	Waterproof DC Connectors (Male and Female) for power supplies and remote receiver
	69-A10	Waterproof 5050 Size LED Red/Green/Blue Connector
	69-A11	3528 Size LED L Connector – For joining strips <b>* For 300 LEDs per Reel ONLY</b>
	69-A12	5050 Size LED L Connector – For joining strips
	69-A13	5050 Size LED Red/Green/Blue L Connector – For joining strips
	69-A14	3528 Size LED T Connector – For joining strips <b>* For 300 LEDs per Reel ONLY</b>
	69-A15	5050 Size LED T Connector – For joining strips
	69-A16	5050 Size LED Red/Green/Blue T Connector – For joining strips
	69-A17	Female DC Connector with 2 ft. leads, 5.5mm x 2.1mm for power supplies and remote receiver
	69-A18	Female DC Connector with 5 ft. leads, 5.5mm x 2.1mm for power supplies and remote receiver
	69-A19	Female DC Connector with 10 ft. leads, 5.5mm x 2.1mm for power supplies and remote receiver
	69-A30	5050 Size LED Red/Green/Blue + White and LED Red/Green/Blue + Warm White Strip Joiner Connector – For joining strips
	69-A31	5050 Size LED Red/Green/Blue + White and LED Red/Green/Blue + Warm White Connector with 6" Leads
	69-A32	5050 Size LED Red/Green/Blue + White and LED Red/Green/Blue + Warm White Strip Jumper Connectors with 5.75" Leads