brainboxes







RoHS Compliant

PX-376

LP PCIe 1xRS422/485 1MBaud Opto Isolated "SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"

ISO 9001



Features

- 1 port RS422/485
- PCI Express x1, x4, x8 x16 lane slots socket size
- 128 Byte Tx and 128 Byte Rx FIFOs
- Up to 921,600 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

Options



PX-376: LP PCIe 1xRS422/485 1MBaud Opto Isolated

Description

Low profile PCI Express Card providing one opto isolated RS422/485 serial port. Data transfer rates up to 921,600 baud rates and the 128 byte deep transmitand 128 byte receive FIFOS, coupled with 1Mbit/s line drivers deliver uncompromising performance on your PC. Drivers for Windows 32 bit and 64 bit Operating Systems including Windows 2000, XP, Server 2003, Vista, Server 2008, Windows 7 and Windows 8.

PCI Express is the latest standard in PC connectivity.

With Brainboxes' industry renowned Lifetime Warranty and Lifetime Support!

Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit 64 bit Editions
- Windows Server 2008 32 bit 64 bit Editions
- Windows Vista 32 bit 64 bit editions
- Windows Server 2003 32 bit 64 bit Editions

As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.





ORDER Description LP PCIe 1xRS422/485 1MBaud Opto Isolated

Code PX-376

+44(0) 151 220 2500 | sales@brainboxes.com | www.brainboxes.com

PX-376



www.brainboxes.com

LP PCIe 1xRS422/485 1MBaud Opto Isolated

PX-376: Full Specification

Port	Ports	1 x RS422/485
Pin 1 TXD- RS422/485 Pinout (9 Pin)	Connector	DB9 Connector - 9 Pin Male
Pin 2 TXD+ Pin 3 RTS-	FIFO size	128 RX FIFO + 128 TX FIFO
Pin 4 RTS+ Pin 5 GND Pin 6 RXD-	Operating Distance	RS422/485 Standard 4000 ft : 1200 metres
Pin 6 RAD- Pin 7 RAD+ Pin 8 CTS Pin 9 CTS+	Cable	No Cable; Integrated Connector
Port Settings	Baud Rate	921,600
921,600 >>>>>>>>>>>>>>>>>>>>>>>>>>>>>>>>>>>	Data Bits	5,6,7 or 8
	Parity	Odd, Even, None, Mark or Space
	Stop Bits	1, 1.5 or 2
	Flow Control	RTS/CTS, DSR/DTR, XON/XOFF
	Tx/Rx Modes	Full Duplex, Half Duplex Autogating
Interface	OS Compatibility	Microsoft Windows 8 32 bit 64 bit Editions
[Fin 1 [7327] R5422/485 Pinost (? Fin)		Microsoft Windows 7 32 bit 64 bit Editions
Fig.1 Fig.1 Fig.3 <th< td=""><td></td><td>Windows Server 2008 32 bit 64 bit Editions Windows Vista 32 bit 64 bit Editions</td></th<>		Windows Server 2008 32 bit 64 bit Editions Windows Vista 32 bit 64 bit Editions
Par 2 (202) Par 1 (212) Par 2 (213) Par 2 (213)		Windows Vista 32 bit 64 bit Editions Windows Server 2003 32 bit 64 bit Editions
	BUS	PCI Express x1, x4, x8 x16 lane slots
Approvals	Other Approvals	AEO C-TPAT Microsoft Certified Gold Partner WEEE RoHS EMC: CE TAA
	Microsoft Approvals	Windows 7 32 bit 64 bit Editions
		Windows Server 2008 32 bit 64 bit editions
		Windows Vista 32 bit 64 bit editions
		Windows Server 2003 32 bit 64 bit editions Windows XP 32 bit 64 bit editions
General	PCB Layers	4
General	Power Consumption	320mA @ 3.3V, 70mA @ 12V
	Weight	0.068 kg
	Size	162 x 18w x 80h mm
Box Content	Packaging	Installation CD including manual, Microsoft signed drivers & utilities
box content	Card	LP PCle 1xRS422/485 1MBaud Opto Isolated
		No Cable; Integrated Connector
Product Support	Warranty	Lifetime (online registration required)
	Support	Lifetime Web, Email and Phone Support from fully qualified, friendly
	55pport	staff who work in and alongside the Product Development Team
Additional	OEM option	Available for bulk buy OEM
	Made In	Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year"
WINNER Manufacturer of the Year Made in the UK	Customisable	Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: sales@brainboxes.com

Other PCI Express Cards: 1 Port RS232 | 2 Port RS232 | 4 Port RS232 | 8 Port RS232 | 1 Port RS422/485 | 2 Port RS422/485 | 4 Port RS422/485 Other Brainboxes Ranges: PCI | Bluetooth Serial Adapter | Ethernet to Serial Adapter | PCMCIA Serial Card | ExpressCard Serial Adapter | USB to Serial

+44(0) 151 220 2500 | sales@brainboxes.com