



Performance:

Meets C3 Standard.

Materials:

- Body : Fireproof ABS UL-94V0
- Jack : 6P6C 6 micro inches gold plated
- PCB : FR-4 / UL-94V0
- IDC Cap : Fireproof ABS UL-94V0
- IDC Body : Fireproof ABS UL-94V0
- IDC Pin : Bronze & Tinned
- Lock Bar : Metal (SPCC)
- Key : Metal (SPCC) & PVC Molding

IDC Description : For 22-26 AWG.
For 110 punch-down Tool

Electrical Specifications:

- Insulation Resistance : 500M ohms (min.)
- Contact Resistance : 20m ohms (max.)
- Current Rating : 1.5 Amps .
- DC Resistance : 0.1 ohms (max.)
- Withstanding Voltage : 1000 VAC RMS @ 60Hz / 1 min.

Mechanical Specifications:

- IDC Punch Down Cycle : Over 250 Cycles (min.)
- Jack Insertion Cycle : Over 2000 Cycles (min.)
- Lock Bar Tension : 15 gms (min.)

Operation Temperature : -40 °C ~ +70 °C

DRAW NO:		ITEM NO:	NLJ-45xx
	APPR	CUSTOMER:	
UNIT: m/m	DESIGN	DATE:	
SCALE: 1:1	Ref. NO:	TOLERANCE:	· ± 1 · X ± 0.2 · XX ± 0.15



Quest Technology International, Inc.
11200NW 138th St., Medley, FL 33178

