



Representative

Catalog Number: 665-SC
Product ID: 7TAA003120R0002
UPC Number: 78599161960
EAN Number: 05415022230178
Status: Active

Four Gang Recessed Service Floor Box, 126 Cubic Inches for Device Access and 40 Cubic Inches for Device Compartments, Length 12-1/8 Inches, Width 12-1/8 Inches, Depth 3-1/2 Inches, Compartment Size Length 5-3/4 Inches, Width 2-3/4 Inches, Depth 2-1/2 Inches, 3/4 Inch and 1-1/4 Inch Knockouts, Galvanized Steel, Delivers Power, Communications and Data from Standard Conduit with No Exposed Service Fittings

- Feed-through from 4 sides allows installer to feed-through power or data/communication services from any orientation
- Total access area of 126 Cubic Inches allows for friendly installation of workstation cables
- Overall height of 3 1/2 Inch allows for shallow pours when needed
- 28 knockouts provide increased flexibility, (16)-1 1/4 Inch and (12)-3/4 Inch
- 4 leveling screws provide 2-1/2 Inch pre-pour adjustment
- Self-leveling covers provide 3/4 Inch after-pour adjustment to accommodate different floor cover thicknesses

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121307 Floor boxes
IGCC	4432 Floor boxes
Brand Name	Steel City
Type	Recessed Service
Special Features	Allows installation of up to 4 device panels in one box
Application	Ideal for the modern office with workstations that have power, communications and data equipment.
Standard	UL E2969
Material	Stamped Steel
Cubic Capacity	126 Cubic Inches
Knockouts	Yes

European Specifications (ETIM)

ETIM	EC000024 Installation box for underfloor-installation
Cover model	Rectangular
Suitable for wet cleaning	Y
Suitable for hollow floor	Y
Material	Other
With opening carpeting	N
Min. built-in depth	3.5mm
Colour	Other
Length external dimension	307.975mm
Width outside dimension	307.975mm

Packaging

Outer Quantity	1
Outer Dimensions (inches)	13x13x4
Weight Uom	9.75 lbs. Each

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta01116-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com