



FEMALE END VIEW



SPECIFICATIONS

HOUSING MATERIAL/COLOR	POLYAMIDE/BLACK
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/FINISH	ALUMINUM/BLACK-ANODIZED
O-RING MATERIAL	BUNA-N
RATED CURRENT [A]	UP to 8.0 A
RATED VOLTAGE [V]	600 V
WIRE SIZE RATING [AWG]	16-22 AWG
CABLE DIAMETER RANGE	5-13mm
TEMPERATURE RATING	-40°C to +90°C (-40°F to +194°F)
PROTECTION CLASS	IP67
TERMINATION TYPE	SCREW TERMINALS



**NOTE
PRELIMINARY
SPECIFICATIONS**

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
	MATERIAL SEE SPECIFICATIONS	DRFT RDS DSGN	DATE 01/18/11 SCALE 1=1.0	DESCRIPTION B 4161-0 5-13MM	
FINISH SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY CONTACT TURCK FOR MORE INFORMATION	UNIT OF MEASUREMENT MILLIMETER [INCH]		IDENTIFICATION NO. U2-18535	REV P2
P2 ADD TERMINATION TYPE	CK 03/23/11 34628	DO NOT SCALE THIS DRAWING		FILE: U2-18535	SHEET 1 OF 1
REV DESCRIPTION	BY DATE ECO NO.				