

Intashield IS-200/IS-250

PCI 2 Port RS232



IS-200 Standard height
Bracket Height = 120mm

• IS-250 Low profile

Bracket Height = 80mm

OPERATING SYSTEMS:

- Windows 7 32bit & 64bit
- Windows Vista 32bit & 64bit
- Windows XP 32bit & 64bit

PRODUCT FEATURES:

- 2x9 pin, D type RS232 Serial Ports
- Low profile card is a 1 + 1 configuration requiring a second bracket for the port on the fly lead
- Universal PCI Bus will fit into any PCI slot 5V or 3.3V
- Fully Plug & Play simple installation and test software provided
- 1 year Warranty with option to sign up for additional free year

SPECIFICATIONS:

UART: 16550

• Speed: 115,200 maximum baud rate

Data Bits: 5, 6, 7 or 8Stop Bits: 1, 1.5 or 2

Parity: odd, even, none, mark or space

• FIFO Size: 16 byte

This card provides 2 industry standard 9 pin RS232 serial COM ports in a single PCI slot.

IS-200

As PCI is fully Plug and Play compatible your BIOS and operating system will automatically configure the card ensuring conflict free installation. Choose between standard height and low profile options.

