

## STANDARD CIRCULAR CONNECTORS





✓ Activ



PRODUCT DRAWING



3D PDF

TE CONNECTIVITY (TE)

T01-0540-S05-FEMALE PLUG CONNECTOR-CRIMP

AMP

1-1437719-4

TE Internal Number: 1-1437719-4 Alias ID: T01-0540-S05

Always EU RoHS/ELV Compliant

Product Type Connector

Shell Material CuZn

Wire/Cable Size (mm²) .14, .25

Wire/Cable Size (AWG) 24

Sealed **Yes** 

Connector Style Receptacle

**Product Drawings** 

T01 FEMALE PLUG CONN. CRIMPVERS. 5 POS. T01 BUCHSENSTECKER

CRIMPVERS. 5 POL.

PDF (TIFF AVAILABLE)

English

T01 FEMALE PLUG CONN. CRIMPVERS. 5 POS. T01 BUCHSENSTECKER

CRIMPVERS. 5 POL.

PDF (TIFF AVAILABLE)

English

T01 FEMALE PLUG CONNECTOR CRIMPV. 3-5 POS. T01 BUCHSENSTECKER

CRIMPV. 3-5 POLIG

PDF **English** 

**CAD Files** 

Customer View Model

3D\_IGS.ZIP English

**Customer View Model** 

3D\_STP.ZIP **English** 

Customer View Model

2D\_DXF.ZIP **English** 

3D PDF

PDF English

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features Product Type Connector

Sealed **Yes** 

	Connector Style Prewired	Receptacle No	
Configuration Features	Number of Positions	5	
Electrical Characteristics	Operating Voltage (VAC)	60	
Body Features	Shell Material  Environmental Protection Type	CuZn Sealed	
Contact Features	Contact Type	Socket	
Housing Features	Centerline (mm)	38	
Dimensions	Wire/Cable Size (mm²) Wire/Cable Size (AWG) Assembly Length (mm)	.14, .25 24 38	
Usage Conditions	Operating Temperature Range (°C)	-40 – 80	
Industry Standards	UL Flammability Rating	UL 94V-2	
Packaging Features	Packaging Quantity	100	
Product Compliance	Statement of Compliance		

## **CUSTOMERS ALSO BOUGHT**

I/O CONNECTOR CONTACTS	I/O CONNECTOR CONTACTS	I/O CONNECTOR CONTACTS	RECTANGULAR CONNECTOR HOUSINGS
T01-CRIMP-S05=TRIAD 5-1437720-7	T01-CRIMP-P03 5-1437720-4	T01-CRIMP-S03 5-1437720-6	HB.6.SGD-LB.2.M25.G 1106418-1
Save to List	Save to List	Save to List	Save to List

VIEW ALL PRODUCT COMPLIANCE

