





CONNETTORE TIPO A (CON MOLLA DI RITEGNO ESTERNA)
CONNECTOR TYPE A (WITH EXTERNAL SPRING)



TIP. CAVITA' PER TERMINALI AMP JPT P/N 929939-...
OPPURE 929937-... E RELATIVI GOMMINI
AMP P/N 828904-1, 828905-1, 282536-1.
TAPPO CAVITA' P/N 828906-2
(TYP. CAV. FOR JPT CONT. P/N 929939-... A/O 929937-... AND REL.
SINGLE WIRE SEAL P/N 828904-1, 828905-1, 282536-1
CAVITY PLUG P/N 828906-2)




NERO (BLACK)	2-282191-1	P	1		
NERO (BLACK)	1-282191-1	-		SUPERSEDED BY 282191-1	
ROSSO (RED)	---			CUSTOMER DWG. FOR REFERENCE ONLY	
GIALLO (YELLOW)	---			DISEGNO PER CLIENTE SOLO PER RIFERIMENTO	
MARRONE (BROWN)	282191-6		3	////	ACCIAIO INOX (STAINLESS STEEL)
BLU (BLUE)	282191-5				MOLLA (SPRING)
VERDE (GREEN)	282191-4		2	NATURALE (NATURAL)	GOMMA SILICONICA (SILICONE RUBBER)
NATURALE (NATURAL)	282191-3				GUARNIZIONE (RUBBER GASKET)
GRIGIO (GREY)	282191-2		1	////	PA 6.6
NERO (BLACK)	282191-1				BLOCCHETTO (HOUSING)
COLORE COLOR	NUMERO PART. N°	ASSY. REV. (ITEM)	N	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)
					DESCRIZIONE (DESCRIPTION)

DIAM. ISOLANTE (INS. DIA. RANGE) 1.5-3.0 (REDUCED INS. CABLE)
RANGO FILO (WIRE RANGE) 0.5-2.5 mm²

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN Ennio CINI NOV. 9'90	STE TE Connectivity
	0 PLC ± -	CHK C.TARTARI 13 OCT 92	
	1 PLC ± 0.3	APVD -	
	2 PLC ± -	PRODUCT SPEC -	
MATERIAL -	FINISH -	APVD -	NAME
		APPLICATION SPEC -	3 W.SPLASH PROOF CONN.ASS'Y with SECONDARY LOCK
		WEIGHT -	SIZE A3 CAGE CODE 00779 DRAWING NO C-282191 RESTRICTED TO -
			CUSTOMER DRAWING SCALE - SHEET 1 OF 2 REV P

1) DIFFERISCE DAL ...-1 ESCLUSIVAMENTE PER IL PACKAGING (DIFFERS FROM ...-1 ONLY FOR PACKAGING DETAILS)
2) PER DIMENSIONI CONTROPARTE VEDERE FOGLIO 2 (FOR COUNTERPART DIMENSIONS SEE SHEET 2)



FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)	CUSTOMER DWG. FOR REFERENCE ONLY	DISEGNO PER CLIENTE SOLO PER RIFERIMENTO
---	---	---	---	---
THIS DRAWING IS A CONTROLLED DOCUMENT.			TE Connectivity	
DIMENSIONS: mm 		NAME 3 POS. SPLASH PROOF CONN. ASS'Y with SECONDARY LOCK		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.3 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 2°		PRODUCT SPEC APPLICATION SPEC SIZE CAGE CODE DRAWING NO RESTRICTED TO A3 00779 C-282191		
MATERIAL FINISH		WEIGHT - CUSTOMER DRAWING SCALE - SHEET 2 OF 2 REV P		