



RECTANGULAR POWER CONNECTORS



TE CONNECTIVITY (TE)

12P UNIV.CAP HSG.

MATE-N-LOK | Universal MATE-N-LOK

926681-3

TE Internal Number: 926681-3

Always EU RoHS/ELV Compliant

Product Type **Housing**

Housing Type **Receptacle**

Connector System **Wire-to-Panel, Wire-to-Wire**

Applies To **Panel, Wire/Cable**

Number of Positions **12**

Active

PRODUCT DRAWING
English

3D PDF

Product Drawings

[12-Pol. UMNL Aufnahmegehäuse UMNL 12-WAY CAP HSG](#)

PDF (TIFF AVAILABLE)
English

[12-Pol. UMNL Aufnahmegehäuse UMNL 12-WAY CAP HSG](#)

PDF (TIFF AVAILABLE)
English

CAD Files

3D PDF

PDF
English

Customer View Model

2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP
English

Customer View Model

3D_STP.ZIP
English

Product Specifications

Product Specification

[Universal MATE-N-LOK Connector](#)

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type

Housing

Housing Type

Receptacle

Contact Type

Pin or Socket

Configuration Features	Number of Positions	12
	Centerline	6.35 mm [.25 in]
	Number of Rows	3
	Row-to-Row Spacing	6.35 mm [.25 in]
	Contact Layout	Matrix
	Multiple Contact Types	Without
Electrical Characteristics	Operating Voltage (VAC)	600
	Operating Voltage (VDC)	600
Contact Features	Contact Retention	Without
Mechanical Attachment	Panel Mount Retention Type	Patch & Tabs
	Panel Mount Retention	With
	Assembly Integration Feature	Without
Housing Features	UL Flammability Rating	UL 94V-0
	Housing Color	Natural
	Housing Material	PA 6.6
Dimensions	Panel Thickness	.76 – 2.29 mm [.03 – .09 in]
Usage Conditions	Sealed Condition	Not Sealed
Operation/Application	Connector System	Wire-to-Panel, Wire-to-Wire
	Applies To	Panel, Wire/Cable
	Operating Temperature	-55 – 125 °C [-67 – 257 °F]
Industry Standards	Glow Wire Rating	Standard Part - Not Glow Wire
	UL Rating	Recognized
	VDE Tested	Yes
	CSA Rating	Certified
	CSA File Number	LR7189
	Agency/Standard Number	E28476
	Agency/Standard	CSA, UL

Packaging Features

Packaging Method

Bag/Box

Packaging Quantity





900

Product Compliance

[Statement of Compliance](#)
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

CUSTOMERS ALSO BOUGHT

CRIMP QUICK DISCONNECTS	RECTANGULAR POWER CONNECTORS	POWER CONTACTS	POWER CONTACTS
			
<p>250 REV FLG FAST REC12-10TPHBZ 61187-1</p>	<p>12P UMNL PLUG HSG UL94VO 350735-4</p>	<p>UNIV.M-N-L.PIN 926886-1</p>	<p>UNIV.M-N-L.PIN 926898-1</p>
<p>Save to List Find Similar Products</p>	<p>Save to List Find Similar Products</p>	<p>Save to List Find Similar Products</p>	<p>Save to List Find Similar Products</p>