

Cable marker - US-WMT (15X4) - 0828767

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)


Cable marker, Card, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Thread on, Cable diameter: 0.6-50 mm, Lettering field: 15 x 4 mm



Why buy this product

- The US-WMT ... UniSheet labeling range includes markers for conductor marking with marking collars from the PATG/PATO ... system
- Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements

Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 559799
Weight per Piece (excluding packing)	11.72 g
Custom tariff number	39204910
Country of origin	Germany

Technical data

Dimensions

Length (b)	15 mm
Width (a)	4.3 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
---------------------------------	------------------

General

Color	white
Components	Silicone-free
Inflammability class according to UL 94	V0
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	84
Number of individual labels per row	14

Cable marker - US-WMT (15X4) - 0828767

Classifications

eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451



Magazine for the THERMOMARK CARD printer, for accommodating US cards