

Protect It! 1-Outlet Surge Protector, Direct Plug-In, 350 Joules, Timer Selection Switch

MODEL NUMBER: SK10TG



Highlights

- 1 outlets/direct plug-in
- 350 joule rating
- Timer selection switch for 1, 3, or 6 hours
- Diagnostic LEDs
- \$5,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)

Package Includes

- SK10TG surge suppressor
- Instruction sheet

Description

The SK10TG surge suppressor with timer offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability and features 1 outlet and 350 joules of surge energy absorption. Timer selection switch for 1, 3, or 6 hours helps make connected devices more energy efficient. On/Off push button lets you shut off outlet at any time. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$5,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only).

Features

- 1 outlets / direct plug-in
- Surge suppression rating: 350 joules
- Timer Feature
- EMI/RFI noise filtering
- Diagnostic LEDs indicate Protected (green) & Grounded (red)
- \$5,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(1) 5-15R
Output (Watts)	1875



Circuit Breaker (amps)	15
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Connection Type	NEMA 5-15P input plug
Input Plug Features	120V, 15A
Input Cord Length (ft.)	0
Input Cord Length (m)	0.00
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Right-Angle Plug	0
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	350
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping Voltage (RMS)	400
AC Suppression Surge Current Rating	27,000
UL1449 Let Through Rating	500, 400, 500
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	0
Cable (Coax) Protection	0
Network (Ethernet) Protection	0
PHYSICAL	
Unit Dimensions (hwd / in.)	2.76 x 2.76 x 1.50
Unit Dimensions (hwd / cm)	7 x 7 x 3.8
Unit Weight (lbs.)	.22
Unit Weight (kg)	.10
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Direct plug-in suppressor mounts directly to a wall receptacle
Housing Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Receptacle Color	Black
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>