LD6A LED SignaLight Towers

Unique Striped Design Improves Visibility

Key features of the LD6A LED SignaLight Towers include:

- The striped design with non-illuminated area between the lenses makes the illuminated color very visible.
- Unique oval lens shape provides high-visibility from different directions
- Five different mounting styles available: frame mount, wall mount, direct mount and pole mount (round or L-shaped bracket).
- Clear lens models available to clearly distinguish between illuminated and non-illuminated lenses.
- Custom configuration is possible.
- Flashing cycle: 1.75Hz (approx. 105 flashes per minute) conforms to international standard IEC 60073.
- Alarm (3.3kHz, 2 different styles) can be heard in 360° degrees.
 Adjustable volume (70 to 90dB).
- Degree of protection: IP65 Steady units and IP54 Flashing units (using frame, wall, direct and pole mount with round base), IP23 Steady and Flashing units using pole mount with L-shaped bracket.





Assembled Products

Mounting Style	Tiers	LED Color Steady		Steady/Flashing/Alarm		
		Code	Part Number	Weight (approx.)	Part Number	Weight (approx.)
	1	R, Y, S, G, W	LD6A-1GQ*-□	220g	LD6A-1GZQ*-□	310g
	2	RY, RG	LD6A-2GQ*-	260g	LD6A-2GZQ*-	350g
G: Frame Mount	3	RYS, RYG	LD6A-3GQ*-	300g	LD6A-3GZQ*-	390g
Wiodit	4	RYSG	LD6A-4GQ*-	340g	LD6A-4GZQ*-	430g
	5	RYSGW	LD6A-5GQ*-	380g	LD6A-5GZQ*-	470g
	1	R, Y, S, G, W	LD6A-1WQ*-□	225g	LD6A-1WZQ*-□	315g
	2	RY, RG	LD6A-2WQ*-	265g	LD6A-2WZQ*-	355g
W: Wall Mount	3	RYS, RYG	LD6A-3WQ*-	305g	LD6A-3WZQ*-	395g
Wiodit	4	RYSG	LD6A-4WQ*-	345g	LD6A-4WZQ*-	435g
	5	RYSGW	LD6A-5WQ*-	385g	LD6A-5WZQ*-	475g
	1	R, Y, S, G, W	LD6A-1DQ*-□	185g	LD6A-1DZQ*-□	275g
	2	RY, RG	LD6A-2DQ*-	225g	LD6A-2DZQ*-	315g
D: Direct Mount	3	RYS, RYG	LD6A-3DQ*-	265g	LD6A-3DZQ*-	355g
Wiodit	4	RYSG	LD6A-4DQ*-	305g	LD6A-4DZQ*-	395g
	5	RYSGW	LD6A-5DQ*-	345g	LD6A-5DZQ*-	435g
	1	R, Y, S, G, W	LD6A-1PQ*-□	645g	LD6A-1PZQ*-□	735g
	2	RY, RG	LD6A-2PQ*-	685g	LD6A-2PZQ*-	775g
P: Pole Mount (with base)	3	RYS, RYG	LD6A-3PQ*-	725g	LD6A-3PZQ*-	815g
(With Bass)	4	RYSG	LD6A-4PQ*-	765g	LD6A-4PZQ*-	855g
	5	RYSGW	LD6A-5PQ*-	805g	LD6A-5PZQ*-	895g
	1	R, Y, S, G, W	LD6A-1KQ*-□	640g	LD6A-1KZQ*-□	730g
K: Pole Mount	2	RY, RG	LD6A-2KQ*-	680g	LD6A-2KZQ*-	770g
(with	3	RYS, RYG	LD6A-3KQ*-	720g	LD6A-3KZQ*-	810g
L-shaped bracket)	4	RYSG	LD6A-4KQ*-	760g	LD6A-4KZQ*-	850g
2.40101	5	RYSGW	LD6A-5KQ*-	800g	LD6A-5KZQ*-	890g



Specify housing color code in place of *: B (black), W (light gray)

Specify illumination color in place of ☐ starting with the top tier. State the LED color code from the left.

R (red), Y (yellow), S (blue),

G (green), W (pure white)
Example: When the LED color is

RYGSW => LD6A-5GQW-

RYGSW => LD6A-5G0 RYGSW

Clear lens type also available.

Specify "C" after the LED color code.

Fxample:

 $\begin{array}{l} \text{LD6A-5GQW-RYSGW} \Rightarrow \\ \text{LD6A-5GQW-RYSGW}\underline{\textbf{C}} \end{array}$



Relays & Sockets

Combination of LED Color and Lens Color

LED Color	Color Lens Type	Clear Lens Type
R: Red	Red lens	Clear lens
Y: Yellow	Yellow lens	Clear lens
S: Blue	Blue lens	Clear lens
G: Green	Green lens	Clear lens
W: White	Clear lens	



For white (W) LED, a clear lens is used in both color and clear lens configurations.

Mounting Parts Included

Signaling Lights

Mounting Style	Supplied Parts
G: Frame mount	M4 screw (4 pcs)*, M4 spring washer (4 pcs)*, M4 plain washer (4 pcs)*, M5 screw (2 pcs), M5 spring washer (2 pcs), M5 plain washer (2 pcs), bracket (1 pc)
W: Wall mount	M4 screw (20 mm) (4 pcs), M4 screw (8 mm) (4 pcs)*, M4 spring washer (8 pcs)* M4 plain washer (8 pcs)*, M4 nut (4 pcs), bracket (1 pc), gasket (1 pc)
D: Direct mount	M5 screw (4 pcs)*, M5 spring washer (4 pcs)*, M5 plain washer (4 pcs)*, M5 nut (4 pcs)*, O-ring (4 pcs), gasket (1 pc)
P: Pole mount (with base)	M5 screw (4 pcs), M5 spring washer (4 pcs), M5 plain washer (4 pcs), M5 nut (4 pcs), O-ring (4 pcs), gasket (1 pc)
K: Pole mount (with L-shaped bracket)	M22 plain washer 2 (pcs), M22 nut (2 pcs), bracket (1 pc)



*For black housing, black screws and washers are supplied. For light gray housing, silver screws and washers are supplied.

Base Module

Style	Mounting Style	Part Number		Notes
Style	Mounting Style	Steady	Steady/Flashing/Alarm	Mores
	Frame Mount	LD6A-0GQ*	LD6A-0GZQ*	
	Wall Mount	LD6A-0WQ*	LD6A-0WZQ*	A top cap is supplied.
	Direct Mount	LD6A-0DQ*	LD6A-0DZQ*	
	Pole Mount (with base)	LD6A-0PQ*	LD6A-0PZQ*	
	Pole Mount (with L-shaped bracket)	LD6A-0KQ*	LD6A-0KZQ*	



Specify a housing color code in place of *: B (black), W (light gray)

Do not supply power to the base module without connecting LED modules.

LED Module

Style		Lens	Part Number	LED Color Code
	Black	Color lens	LD9Z-6ALB-□	R, Y, S, G, W
		Clear lens	LD9Z-6ALB- □ C	R, Y, S, G
	Light grove	Color lens	LD9Z-6ALW-□	R, Y, S, G, W
	Light gray	Clear lens	LD9Z-6ALW-□C	R, Y, S, G



Specify an LED color code in place of \square : R (red), Y (yellow), S (blue), G (green), W (white) When using white (W) with a clear lens, order LD9Z-6ALB-W (black housing) or LD9Z-6ALW-W (light gray housing).

Center Set Screw

Item		Part Number	Notes
	1 tier	LD9Z-6AC1	
6-	2 tiers	LD9Z-6AC2	
	3 tiers	LD9Z-6AC3	A plain washer and spring washer are supplied.
00	4 tiers	LD9Z-6AC4	
	5 tiers	LD9Z-6AC5	

Relays & Sockets

Ordering Examples

When ordering LD6A-3PQW-RYG as sub-component parts, specify the following:

Pole mount (with base), steady, light gray housing, 3 tiers, color lens LED mo	dules with Ked, Yellow, an	id Green LED
Base module (pole mount with base, steady, light gray housing)	LD6A-0PQW	1 piece
LED module (red LED with color lens, light gray housing)	LD9Z-6ALW-R	1 piece
LED module (yellow LED with color lens, light gray housing)	LD9Z-6ALW-Y	1 piece
LED module (green LED with color lens, light gray housing)	LD9Z-6ALW-G	1 piece
Center screw set (3 tiers)	LD9Z-6AC3	1 piece

[Ex. 2]

When ordering LD6A-5WZQB-RYSGWC as sub-component parts, specify the following: Wall mount, steady/flashing/alarm, black housing, 5 tiers, clear lens LED modules with Red, Yellow, Blue, Green, and Pure white LED

Signaling Lights

Base module (wall mount, steady/flashing/alarm, black housing)	LD6A-0WZQB	1 piece
LED module (red LED with clear lens, black housing)	LD9Z-6ALB-RC	1 piece
LED module (yellow LED with clear lens, black housing)	LD9Z-6ALB-YC	1 piece
LED module (blue LED with clear lens, black housing)	LD9Z-6ALB-SC	1 piece
LED module (green LED with clear lens, black housing)	LD9Z-6ALB-GC	1 piece
LED module (pure white LED with clear lens, black housing)	LD9Z-6ALB-W	1 piece
Center screw set (5 tiers)	LD9Z-6AC5	1 piece

Replacement Parts

Item	Description		Part Number	Notes
	Тор Сар	Black	LD9Z-6ATB	A tan again annalised with a base module
		Light gray	LD9Z-6ATW	A top cap is supplied with a base module.
30	L-shaped Bracket	Metal (chrome-plated)	LD9Z-6AK	Two plain washers and two nuts are supplied.



Specifications

Specifications

Safety Standards	IEC60947-5-1, EN60947-5-1, UL508, CSA C22.2 No.14				
Operating Temperature	-25 to +55°C (no freezing)				
Operating Humidity	45 to 85% RH (no condensation)			
Storage Temperature	-40 to +75°C (n	o freezing)			
Overvoltage Category	III (IEC60664-1)				
Impulse Withstand Voltage	800V (IEC60947	7-1)			
Insulation Resistance	100 MΩ minim	um (500V DC megger)			
Dielectric Strength	Between live a	nd dead parts: 1000V AC, 1 minute			
Pollution Degree	3				
Corrosion Immunity	Atmosphere free from corrosive gases				
Vibration Resistance	Operating extre	emes: 10 to 55Hz, amplitude 0.5 mm			
Shock Resistance	Operating extre	emes: 147 m/s², 6 shocks each in 6 axe	S		
	Steady	frame mount, wall mount, direct mount, pole mount with base	IP65		
Degree of Protection	Steady	pole mount with L-shaped bracket	IP23		
(IEC60529)	Flashing/ Alarm	frame mount, wall mount, direct mount, pole mount with base	IP54		
	Flashing/ Alarm	pole mount with L-shaped bracket	IP23		
Housing Color	Black, Light gra	у			
Material	Housing: ABS resin Lens: AS resin Pole: Steel (nickel-chrome plated) Pole base: Diecast aluminum				
Wire	22AWG				

Functional Specifications

	unononal opcomounons						
Rate	ed Insulation Voltage	60V					
Ope	rating Voltage	24V AC/DC ±10%					
Rate	ed Voltage (Ue)	24V AC/DC					
LED	Color Code	R (red), Y (yellow)	, S (blue), G (green)	, W (white)			
	Illumination Color	R, Y	S, G	W			
ED	Rated Current (per tier)	25mA	30mA	20mA			
_	Power Consumption (per tier)	0.6W	0.75W	0.5W			
LED	Life (Note)	Approx. 30,000 hours (until brightness is reduced to 50% of the initial value in a 25°C operating environment)					
Flas	shing Cycle (IEC60073)	Approx. 105 flashes per minute (1.75 Hz)					
	Alarm Cycle	Alarm 1: approx. 700 times per minute Alarm 2: approx. 35 times per minute					
Æ	Current Draw	110mA max.					
Alarm	Inrush Current	AC: 400mA max. DC: 250mA max.					
	Alarm Volume	70 to 90dB, at 1m	(volume adjustable	e)			
	Acoustic Frequency	Approx. 3.3kHz					

Note: Life of the LED varies according to operating conditions and environment.

External Contact Ratings

	AC Contact Capacity	Current Capacity	100mA min.
	(per tier)	Dielectric Strength	35V AC min.
田		Current Capacity	100mA min.
	DC Contact Capacity, Transistor Capacity (per tier)	Dielectric Strength	35V min.
	manufactor dupatity (por tion)	Leakage Current	0.1mA max.
	AC Contact Capacity	Current Capacity	400mA min.
_	(per alarm)	Dielectric Strength	35V AC min.
Alam	DC Contact Capacity,	Current Capacity	300mA min.
_	Transistor Capacity (per alarm)	Dielectric Strength	35V min.
		Leakage Current	0.1mA max.

Dimensions (Steady Light) Frame Mount Wall Mount Direct Mount Pole Mount (with base) Pole Mount (with L-shaped bracket)

Signaling Lights

Front


Dimension Table


Conduit Port


M20×P1.5

Difficusion rapie						
	Tiers	Frame Mount	Wall Mount	Direct Mount (L3)	Pole Mount	
	Hers	(L1)	(L2)		w/ base (L4)	w/ L-shaped bracket (L5)
	1	156	156	98	408	372
	2	186	186	128	438	402
	3	216	216	158	468	432
	4	246	246	188	498	462
	5	276	276	218	528	492


Panel Cut-Out












Dimension Table

Tions	Frame Mount	Wall Mount	Direct Mount (L3)	Pole Mount	
Tiers	(L1)	(L2)		w/ base (L4)	w/ L-shaped bracket (L5)
1	228	228	170	480	444
2	258	258	200	510	474
3	288	288	230	540	504
4	318	318	260	570	534
5	348	348	290	600	564

Panel Cut-Out



*Complies with IEC60947-5-1.

Wiring Example (Flashing Light and Alarm)

Mechanical Contacts LED Red: Red LED Yellow: Orange Red LED Blue: Blue Yellow Blue LED Pure White: Whit Alarm 1: Purple Green Alarm 2: Light Blue Pure White External contact for flashing light Flashing COM: Brown Gray Power supply Fuse 1A

External contact for steady light/ala Red LED Yellow: Orange LED Blue: Blue Yellow LED Green: Green Blue LED Pure White: White Alarm1: Purple Green Alarm 2 Light Blue ____contact for flashing light

Gray

Yellow

Fuse 1A

NPN Transistors

Power

Power


Signaling Lights

PNP Transistors Red LED Yellow: Orange LED Blue: Blue Yellow LED Green: Green Blue LED Pure White: White Alarm1: Purple Green Alarm 2 Light Blu Pure White Power Gray Fuse 1A Power Yellow

Safety Precautions

- Turn off the power to the LD6A before mounting, removing, wiring or assembling the LED module. Make sure the wiring is done correctly otherwise electrical shock or fire may result.
- Mount the LD6A on a solid surface not subject to vibrations.
- Do not mount the LD6A upside-down or horizontally.
- · Do not leave the LD6A without a cap or unassembled.
- Install the supplied gasket, otherwise the waterproof seal will be compromised.

- Do not apply any chemicals that may corrode the plastic materials.
- If the LD6A is subjected to strong vibrations, the hexagon socket screw may become loose. Take measures to prevent loosening. (See the figure below.)



· Do not loosen any screws if the tightening torque is not specified.

Instructions

Examples of recommended frames and frame nuts

Frame Size	Frame	Frame Nut	Manufacturer	
□ 30 mm*	SFF-302	SFB-001 SFB-4B5 SFB-101	SUS	
□ 40 mm	SFF-402	SFB-008 SFB-4A5 SFB-108	Corporation (Japan)	

^{*}The mounting bracket for the housing is 40 mm.

For panel cut-out dimensions, see pages 9 and 10.


See drawing below regarding the mounting of the LD6A.

- · Postion the LD6A to make sure the alarm sound is the loudest. (Steady/flash-
- ing/alarm type)

Frame Mounting

Mounting

- 1. Insert two nuts in the frame, and attach the bracket using two M5 screws. Recommended tightening torque: 2.6 to 2.7 N·m
- 2. Mount the LD6A to the bracket using four M4 screws. Recommended tightening torque: 1.6 to 1.7 N·m



Note: See table below for typical examples of frames and nuts. Consult the manufacturer of the frame for the installation method of the frame nut.

When using a frame mount type, be sure to use flexible conduit, otherwise the waterproof seal will be compromised.

Refer to the "Example of Flexible Conduit" shown on the right.


Example of Flexible Conduit

Example of Floxible conduit		
	Conduit Port Size	M20
	Gland	AL16/M20/A/BL
	Conduit	PAFS16BL
	Manufacturer	Adaptaflex




Wall Mounting

- 1. Make four tapped holes in the mounting panel and mount the bracket and gasket using four screws (M4 x 20). Recommended tightening torque: 1.6 to 1.7 N·m
- 2. Mount the LD6A to the bracket using four screws (M4 x 8). Recommended tightening torque: 1.6 to 1.7 N·m



Direct Mounting


Recommended tightening torque: 2.6 to 2.7 N·m



Pole Mounting (with base)

The pole mount type can be installed in four ways. The recommended mounting method (pattern A from page 9 or 10) is described below.

Recommended tightening torque: 2.6 to 2.7 N·m (M5 screw)



Pole Mounting (with L-shaped bracket)


1. Using L-shaped bracket

Recommended tightening torque: 10 to 11 N·m (M10) Recommended tightening torque: 25 to 26 N·m (M22)

2. Not using L-shaped bracket

Remove the bushing, hexagonal nut (M22), plain washer, and L-shaped bracket from the LD6A and install in the following order: plain washer, hexagonal nut (M22), and bushing.

Recommended tightening torque: 25 to 26 N·m (M22)




The parts marked with * are not supplied and should be provided by the user.

Replacement and Addition of LED Modules

• Make sure to turn power off.

Signaling Lights

- Insert a flat screwdriver into the cap recess as shown below, lift up the cap, and remove with your hands. Use a flat screwdriver with maximum 1-mm thick and 7-mm wide tip.
- Remove the center screw before reassembling the LED modules.
- When assembling the LED modules, make sure to align the recess of the cap with the recess of the LED module. Otherwise, damage may result. Recommended tightening torque: 0.4 to 0.5 N·m.



- Note the correct orientation when assembling the LED modules.
- Tighten the screws to the recommended tightening torque. The LED module may be damaged if the screw is loose during operation.
- Do not touch the metal plug on the LED module. Otherwise, LED elements maybe damaged due to static electricity.
- Use a maximum of 5 tiers.
- Select the correct screw length depending on the number of tiers.
- Do not remove the gasket from the LED module. Otherwise, the waterproof seal will be compromised.

Wiring

- · For wiring, see the wiring diagrams on pages 708 and 710.
- Incorrect wiring may damage the internal circuit.
- · Be sure to insulate unused wires.
- Connect a 1A fuse to the power line as shown in the Wiring Examples on pages 708 and 710.
- Use a UL listed external fuse holder.
- Use a class 2 power supply only.
- When using LED modules of the same color for two or more tiers, determine contact capacity in referencet to the LED current, because only one wire is used to light all tiers of the same color.
- Do not apply voltage to flashing (brown) lines.
- · Do not connect flashing (brown) line to the power lines. The internal circuit may be damaged.
- Do not turn on steady and flashing circuits simultaneously.
- Do not turn on alarms 1 and 2 simultaneously.



Wire Color


Wire Color	Steady	Steady, Flashing, Alarm
Red	LED Module – Red	LED Module – Red
Orange	LED Module – Yellow	LED Module – Yellow
Blue	LED Module – Blue	LED Module – Blue
Green	LED Module – Green	LED Module – Green
White	LED Module – White	LED Module – White
Purple	_	Alarm 1
Light Blue	_	Alarm 2
Brown	_	Flashing COM
Gray	_	Power Line
Yellow	Power Line	Power Line



For information on external contacts, see "External Contact Ratings" on page 707.

Alarm Volume Adjustment

- Move the volume adjustment to the right or left to change the volume.
- When the adjustment lever is all the way to the right the volume is at its maximum.
- The adjustment lever may be damaged if forced open or closed.



High Temperature Limitations

The external temperature cannot exceed 50°C when all tiers are lit at the same time in the following combinations:

- Three tiers
 Two or more tiers of blue and green (example: Red-Green-Blue, Green-Green-Red)
- 2. Four or five tiers (example: Red-Yellow-Green-White, Red-Yellow-Blue-Green-White)