

5349560-1 Product Details

[Share](#) |
 [Print](#) |
 [Email](#)



5349560-1

Fiber Optic Cable Assemblies

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Single Fiber
- Cable Assembly
- ST Fiber Optic Cable Connector Type
- Fiber Type = 50/125 Micron
- Cable Assembly Type = ST-Style (2.5mm Bayonet) to ST-Style (2.5mm Bayonet)

[View all Features](#)

TE Internal Number: 5349560-1

[Active](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

<p>Product Drawings:</p> <ul style="list-style-type: none"> • FOMM50 LEAD 2,5S ST - ST (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Related Products:</p> <ul style="list-style-type: none"> • Tooling
--	---

[List all Documents](#)

Feedback

Product Features (Please use the Product Drawing for all design activity)

<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Designation = Single Fiber • Product Type = Cable Assembly • Fiber Optic Cable Connector Type = ST • Cable Assembly Type = ST-Style (2.5mm Bayonet) to ST-Style (2.5mm Bayonet) • Cable Type = Simplex <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Insertion Loss (dB) = 0.30 <p>Termination Features:</p> <ul style="list-style-type: none"> • Fiber Type (Micron) = 50/125 <p>Dimensions:</p> <ul style="list-style-type: none"> • Cable Diameter (mm [in]) = 2.50 [.098] • Length (M [ft]) = 1.00 [3.281] <p>Body Features:</p> <ul style="list-style-type: none"> • Cable Color = Orange • Boot Body Style - Left = Standard • Boot Color - Left = Black • Boot Body Style - Right = Standard • Boot Color - Right = Black • Ferrule Material = Ceramic 	<p>Contact Features:</p> <ul style="list-style-type: none"> • Fibre Channel = No <p>Configuration Features:</p> <ul style="list-style-type: none"> • Mode = Multimode • Number of Fibers = 1 • Cable Buffering = Tight Buffered Easy Strip • Connector(s) Exit Angle to Connector(s) Exit Angle = 180° to 180° <p>Industry Standards:</p> <ul style="list-style-type: none"> • Flammability Rating Type = LSZH (Low Smoke Zero Halogen) • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant <p>Product Availability:</p> <ul style="list-style-type: none"> • Region = Not Specified <p>Other:</p> <ul style="list-style-type: none"> • Brand = TE Connectivity
--	---

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[AODA Accessibility Policy](#)
[AODA Multi-Year Accessibility Plan](#)

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

