



## 5349560-2 Product Details



### 5349560-2

TE Internal Number: 5349560-2

**Active**

### Fiber Optic Cable Assemblies

Always EU RoHS/ELV Compliant (Statement of Compliance)

**Product Highlights:**

- Single Fiber
- Cable Assembly
- ST Fiber Optic Cable Connector Type
- Fiber Type = 50/125 Micron
- Cable Assembly Type = ST-Style (2.5mm Bayonet) to ST-Style (2.5mm Bayonet)

[View all Features](#)
**Quick Links**

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information	
<b>Product Drawings:</b> <ul style="list-style-type: none"> <li>• <a href="#">FOMM50 LEAD 2,5S ST - ST</a> (PDF, English)</li> </ul> <b>Catalog Pages/Data Sheets:</b> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <b>Product Specifications:</b> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <b>Application Specifications:</b> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <b>Instruction Sheets:</b> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <b>CAD Files:</b> <ul style="list-style-type: none"> <li>• None Available</li> </ul>	<b>Related Products:</b> <ul style="list-style-type: none"> <li>• <a href="#">Tooling</a></li> </ul>
<a href="#">List all Documents</a>	

Product Features (Please use the Product Drawing for all design activity)	
<b>Product Type Features:</b> <ul style="list-style-type: none"> <li>• <a href="#">Product Designation</a> = Single Fiber</li> <li>• Product Type = Cable Assembly</li> <li>• <a href="#">Fiber Optic Cable Connector Type</a> = ST</li> <li>• Cable Assembly Type = ST-Style (2.5mm Bayonet) to ST-Style (2.5mm Bayonet)</li> <li>• Cable Type = Simplex</li> </ul> <b>Electrical Characteristics:</b> <ul style="list-style-type: none"> <li>• Insertion Loss (dB) = 0.30</li> </ul> <b>Termination Features:</b> <ul style="list-style-type: none"> <li>• <a href="#">Fiber Type (Micron)</a> = 50/125</li> </ul> <b>Dimensions:</b> <ul style="list-style-type: none"> <li>• Cable Diameter (mm [in]) = 2.50 [.098]</li> <li>• Length (M [ft]) = 2.00 [6.56]</li> </ul> <b>Body Features:</b> <ul style="list-style-type: none"> <li>• Cable Color = Orange</li> <li>• Boot Body Style - Left = Standard</li> <li>• Boot Color - Left = Black</li> <li>• Boot Body Style - Right = Standard</li> <li>• Boot Color - Right = Black</li> <li>• Ferrule Material = Ceramic</li> </ul>	<b>Contact Features:</b> <ul style="list-style-type: none"> <li>• Fibre Channel = No</li> </ul> <b>Configuration Features:</b> <ul style="list-style-type: none"> <li>• <a href="#">Mode</a> = Multimode</li> <li>• Number of Fibers = 1</li> <li>• Cable Buffering = Tight Buffered Easy Strip</li> <li>• Connector(s) Exit Angle to Connector(s) Exit Angle = 180° to 180°</li> </ul> <b>Industry Standards:</b> <ul style="list-style-type: none"> <li>• Flammability Rating Type = LSZH (Low Smoke Zero Halogen)</li> <li>• <a href="#">RoHS/ELV Compliance</a> = RoHS compliant, ELV compliant</li> <li>• <a href="#">Lead Free Solder Processes</a> = Not relevant for lead free process</li> <li>• RoHS/ELV Compliance History = Always was RoHS compliant</li> </ul> <b>Product Availability:</b> <ul style="list-style-type: none"> <li>• Region = Not Specified</li> </ul> <b>Other:</b> <ul style="list-style-type: none"> <li>• Brand = AMP</li> </ul>

[Feedback](#)

[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)  
[AODA Accessibility Policy](#)  
[AODA Multi-Year Accessibility Plan](#)

[Distributor Inventory](#)  
[Product Cross Reference](#)  
[Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Knowledge Base](#)  
[Manage Your Account](#)

