



5349560-3 Product Details

[Share](#) [Print](#) [Email](#)


5349560-3

Fiber Optic Cable Assemblies

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Single Fiber
- Cable Assembly
- ST Fiber Optic Cable Connector Type
- Fiber Type = 50/125 Micron
- Cable Assembly Type = ST-Style (2.5mm Bayonet) to ST-Style (2.5mm Bayonet)

[View all Features](#)

TE Internal Number: 5349560-3

Active

Add to My Part List	Request Sample	Find Similar Products	Buy Product
-------------------------------------	--------------------------------	---------------------------------------	-----------------------------

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [FOMM50 LEAD 2,5S ST - ST](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Feedback

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Designation](#) = Single Fiber
- Product Type = Cable Assembly
- [Fiber Optic Cable Connector Type](#) = ST
- Cable Assembly Type = ST-Style (2.5mm Bayonet) to ST-Style (2.5mm Bayonet)
- Cable Type = Simplex

Electrical Characteristics:

- Insertion Loss (dB) = 0.30

Termination Features:

- [Fiber Type \(Micron\)](#) = 50/125

Dimensions:

- Cable Diameter (mm [in]) = 2.50 [.098]
- Length (M [ft]) = 3.00 [9.842]

Body Features:

- Cable Color = Orange
- Boot Body Style - Left = Standard
- Boot Color - Left = Black
- Boot Body Style - Right = Standard
- Boot Color - Right = Black
- Ferrule Material = Ceramic

Contact Features:

- Fibre Channel = No

Configuration Features:

- [Mode](#) = Multimode
- Number of Fibers = 1
- Cable Buffering = Tight Buffered Easy Strip
- Connector(s) Exit Angle to Connector(s) Exit Angle = 180° to 180°

Industry Standards:

- Flammability Rating Type = LSZH (Low Smoke Zero Halogen)
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Product Availability:

- Region = Not Specified

Other:

- Brand = AMP

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[AODA Accessibility Policy](#)
[AODA Multi-Year Accessibility Plan](#)

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

